

# Handheld Pressure Manometer **multicomp** PRO

**RoHS  
Compliant**



## Features:

- Easy to operate, reliable, and robust
- Gauge/Differential pressure ranges from 0 to 5 psi
- 11 selectable pressure units - psi, bar, mbar, kPa, inH<sub>2</sub>O, cmH<sub>2</sub>O, ftH<sub>2</sub>O, inHg, mmHg, ozin<sup>2</sup>, kgcm<sup>2</sup>
- Data Hold function
- Auto Power Off disabled
- USB to collect readings to a PC using the included software

## Specifications

Function	Range	Resolution	Function	Range	Resolution
inH <sub>2</sub> O	138.3	0.1	ozin <sup>2</sup>	80.00	0.01
psi	5.000	0.001	FtH <sub>2</sub> O	11.53	0.01
mbar	344.7	0.1	cmH <sub>2</sub> O	351.5	0.1
kPa	34.47	0.01	kgcm <sup>2</sup>	0.351	0.001
inHg	10.18	0.001	Bar	0.344	0.001
mmHg	258.5	0.1			
Display	Dual LCD				
Accuracy	±0.3%FSO (25°C)				
Repeatability	±0.2% (Max. ±0.5%FSO)				
Linearity / Hysteresis	±0.29% FSO				
Pressure Range	±5 psi				
Maximum Pressure	20psi				
Response Time	0.5 seconds typical				
Zero Adjust and Offset	Yes				
Data Hold	Yes				
Auto Power Off	Yes				
Low Battery Indicator	Yes				
Over Range Indicator	Err.1				
Under Range Indicator	Err.2				
Operation Conditions	0°C to 50°C				
Storage Conditions	-10°C to 60°C				
Power Supply	The Pressure Manometer comes with an external 9V DC power supply, featuring both EU and UK plugs, and includes a 9V battery.				

## Part Number Table

Description	Part Number
Handheld Pressure Manometer, 5psi	MP780649

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO