

# UBE/D + ES/KMK 3 - Marker carriers



1004076

<https://www.phoenixcontact.com/in/products/1004076>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker carriers, for identifying terminal groups, for mounting on the NS 32 or NS 35/7,5 terminal strip, gray, unlabeled, mounting type: snapped, lettering field size: 40 x 17 mm



## Commercial data

Item number	1004076
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2
Product key	BG211A
GTIN	4017918011888
Weight per piece (including packing)	10.31 g
Weight per piece (excluding packing)	10.09 g
Customs tariff number	39269097
Country of origin	IN

1004076

<https://www.phoenixcontact.com/in/products/1004076>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	20 mm
Text field width	40.00 mm
Height	51.5 mm
Height NS 35/7,5	51.5 mm
Text field height	17.00 mm
Length	42.5 mm

### Material specifications

Color	gray
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Mounting

Mounting type	snapped
---------------	---------

# UBE/D + ES/KMK 3 - Marker carriers



1004076

<https://www.phoenixcontact.com/in/products/1004076>

## Classifications

### ECLASS

ECLASS-11.0	27281105
ECLASS-12.0	27281105
ECLASS-13.0	27281105

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UBE/D + ES/KMK 3 - Marker carriers



1004076

<https://www.phoenixcontact.com/in/products/1004076>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)