

3ft (1m) UK Computer Power Cable, BS 1363 to C13, 18AWG, 10A 250V, Replacement AC Power Cord, Kettle Lead / UK Power Cord, PC Power Supply Cable, TV Power Cable

**Product ID:** BS13U-1M-POWER-LEAD



The BS13U-1M-POWER-LEAD UK Computer Power Cord features one BS 1363 plug and one C13 receptacle. It is a suitable replacement cable for worn-out or missing PC power cords.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

## Certifications, Reports and Compatibility



## Applications

## Features

- **AC POWER CABLE:** This 1m (3.3ft) 18AWG (0.75mm) flexible computer power cable with BS 1363 and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 250V at 10A.
- **PERFORMANCE AND SAFETY:** Fully molded strain reliefs for durability and VDE approved connectors. 3 conductor power cable made from 100% copper wire. Fire Rating: VW-1.
- **SPECS:** 3.3ft (1m) Power Cord. BS 1363 to IEC 60320 C13. 18AWG (0.75mm). 250V 10A (Max). Jacket Rating: H05VV-F. Jacket Material: PVC. Color: Black. Temperature Range: -10 to 35C. Cable Outer Diameter: 6.8mm.
- **COMPATIBILITY:** BS 1363 works with UK electrical outlets. IEC C13 connector works with most desktop.

computers, monitors, printers, and other devices featuring a C14 inlet Replacement PC power supply cable/cord, Kettle Lead

- THE IT PRO'S CHOICE: Designed for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This UK power cord is also available in 1.8m and 3m

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SVT

---

#### Connector(s)

Connector A	1 - BS 1363 Power (UK)
Connector B	1 - IEC 60320 C13 Power

---

#### Power

Input Voltage	250 AC
Input Current	10 A

---

#### Environmental

Operating Temperature	-10C to 35C (14F to 95F)
Storage Temperature	-15C to 70C (5F to 158F)
Humidity	5% ~ 95%

---

#### Physical Characteristics

Color	Black
Wire Gauge	0.75mm <sup>2</sup>
Cable Length	3.3 ft [1 m]
Product Length	1.8 in [4.5 cm]
Product Width	39.4 in [100.0 cm]
Product Height	2.0 in [5.0 cm]
Weight of Product	6.0 oz [171.0 g]

---

**Packaging  
Information**

Package Quantity	1
Package Length	11.4 in [29.0 cm]
Package Width	5.5 in [14.0 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	6.3 oz [178.0 g]

---

**What's in the Box**

Included in Package	1 - 1m UK Computer Power Cord - C13 to BS-1363
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***