

HDMI to RCA Converter Box with Audio

Product ID: HD2VID2



This HDMI to RCA converter box with audio converts a digital HDMI video source (with supporting audio) to work with analog RCA composite video televisions and displays, in both NTSC and PAL systems.

This HDMI to composite video converter provides features that ensure the highest quality output image, such as noise reduction, frame rate conversion and adaptive contrast enhancement.

With support for high-definition input resolutions up to 1080p, this RCA adapter lets you convert your HDMI signal to composite video and audio while still producing a crystal-clear picture.

This lightweight composite adapter is compact and highly portable, so you can use it virtually anywhere. Offering support for a wide range of HDTV and PC input resolutions, this versatile RCA converter is a perfect solution for using newer devices with your existing legacy displays.

The ability to convert and use your new HDMI equipped device with your older televisions or displays not only offers flexibility but also saves you the cost of upgrading hardware, making it extremely convenient for home or office applications.

To ensure easy operation and installation, this unique RCA composite video converter allows for plug-and-play installation without any additional software or drivers.

HD2VID2 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Convert your HDMI signal to RCA composite video
- Continue to use standard definition displays with HDMI source devices
- Ideal for presentations that use dated projection systems
- Stream your new home videos onto your older TVs/displays

Features

- Convert your current HDMI source to composite video and audio (yellow, white and red outputs)
- Achieve HDTV resolutions with support for up to 1080p
- Support for multiple HDTV and PC input resolutions, compatible with almost any HDMI source device
- Hassle-free setup with simple plug-and-play installation

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	HDMI
AV Output	Composite
	Audio RCA
Audio	Yes
Industry Standards	Standard HDMI, DVI 1.0

Performance

Supported Resolutions	Input
	TV - 1080p, 720p, 576p, 480p @ 60Hz
	PC - 1920x1080, 1280x800, 1280x768, 1224x768, 800x600, 640x480 @ 60Hz
	Output
	480i, 576p
Audio Specifications	Input - LPCM 2Ch, 48kHz
	Output - Stereo L/R

MTBF 1,301,084 hours

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - Composite Video (1 x RCA)
Input Connector(s)	1 - Stereo Audio (2 x RCA)

Indicators

LED Indicators	1 - Input LED
	1 - Power LED

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4 A
Output Voltage	5 DC
Output Current	1000 mA
Plug Type	M

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	20~90% RH

Physical Characteristics

Color	Black
Material	Steel
Product Length	4.3 in [10.8 cm]
Product Width	3.9 in [10.0 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	10.1 oz [286.0 g]

Packaging Information

Package Quantity	1
Package Length	8.4 in [21.4 cm]
Package Width	6.0 in [15.2 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package) Weight	1.2 lb [0.5 kg]

What's in the Box

Included in Package	1 - HDMI to Composite Converter
	1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
	4 - Screws
	2 - Mounting Brackets
	1 - User Manual

****Product appearance and specifications are subject to change without notice.***