

1m (3ft) Power Extension Cord, C14 to C13, 10A 125V, 18AWG, Computer Power Cord Extension, IEC-320-C14 to IEC-320-C13 AC Power Cable Extension for Power Supply, UL Listed

**Product ID:** PXT1001M



The PXT1001M 1m PDU Style Computer Power Extension Cord features one C13 computer power (female) connector and one C14 hooded (male) power connector, and enables you to connect your server to a C13-equipped UPS or PDU.

This high quality C13 to C14 Power Cord Extension Cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Extend the power connection from your server to a PDU by up to 1-meter

## Features

- **AC POWER CORD:** This 1m (3.3ft) 18AWG power supply extension cable with IEC 60320 C14 and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A.
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. Fire Rating: VW-1. 3 Conductor extension cord made with 100% copper wire. This C14 to C13 power extension cord is available in other lengths.

- **SPECS:** 1m (3.3ft) AC Power Cord IEC 60320 C14 to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 works with North American outlets IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride

---

#### Connector(s)

Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C14 Power

---

#### Special Notes / Requirements

Note	UL Listed
------	-----------

---

#### Power

Input Voltage	125 AC
Input Current	10A

---

#### Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	3.3 ft [1 m]
Product Length	39.4 in [100.0 cm]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.1 cm]
Weight of Product	3.8 oz [109.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	4.1 oz [117.0 g]

---

**What's in the Box**

Included in Package	1 - 1m Standard Computer Power Cord Extension - C14 to C13
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***