



|                        |   |                               |          |
|------------------------|---|-------------------------------|----------|
| <b>EAN:</b>            | 4013288229922                                       | <b>Size:</b>                  | 0x0x0 mm |
| <b>Part number:</b>    | 05006607001   | <b>Weight:</b>                | 0 g      |
| <b>Article number:</b> | Kraftform Kompakt VDE 16<br>Universal 1 Tool Finder | <b>Country of origin:</b>     | CZ       |
|                        |   | <b>Customs tariff number:</b> | 82054000 |

- VDE-insulated Kraftform 817 VDE bitholding screwdriver with anti-roll protection
- Hexagonal anti-roll feature against rolling away
- Individually tested tool as per IEC 60900 at 10,000V
- In robust pouch
- Suitable for Wera 2go

One 817 VDE Kraftform bitholding screwdriver, 14 VDE blades with "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool, one single-pole phase tester. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. In a robust belt pouch. The textile box features a fleece zone at the back. Using the provided self-adhesive hook and loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.

**Web link**

Wera - Kraftform Kompakt VDE 16 Universal 1 Tool Finder  
05006607001 - 4013288229922

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

**Individually tested**



Why is the right tool so often missing at the workplace? The reason: too many tools and overly-heavy tool bags can make it bothersome to carry keep them with you. So for us it was a clear challenge: to develop a tool that is suitable for a whole host of applications and can be easily taken along to the workplace. Our solution: Kraftform Kompakt tools. A handle into which blades with a range of different profiles can be inserted. Compactly and protectively housed in a light and robust textile pouch - and they are even VDE-tested, too.




Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

**Handle/interchangeable blade system – Kraftform Kompakt VDE**



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

**Easy change**




The Kraftform Kompakt VDE blades can be replaced simply by pulling down the yellow ring on the handle.

**PlusMinus screwdrivers**




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

**“Take it easy”**




The Kraftform Kompakt VDE blades are equipped with the "Take it easy" Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

**Hexagonal anti-roll feature against rolling away**



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

**Fast spinning**



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.


**Web link**

Wera - Kraftform Kompakt VDE 16 Universal 1 Tool Finder  
05006607001 - 4013288229922

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de


Set contents:

**817 VDE Kraftform blade-holding handle, 9 x 98 mm**

 05003990001 1x 9 x 98 mm



**Kraftform Kompakt VDE 62 i Take it easy, PH 1 x 157 mm**

 1x PH 1 x 157 mm  
1x PH 2 x 157 mm



**Kraftform Kompakt VDE 65 i Take it easy, PZ 1 x 157 mm**

 1x PZ 1 x 157 mm  
1x PZ 2 x 157 mm



**Kraftform Kompakt VDE 65 i PZ/S Take it easy, # 1 x 157 mm**

 1x # 1 x 157 mm  
1x # 2 x 157 mm




**Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm**

 1x TX 10 x 157 mm  
1x TX 15 x 157 mm  
1x TX 20 x 157 mm  
1x TX 25 x 157 mm




**Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm**

 1x 0.4 x 2.5 x 157 mm  
1x 0.6 x 3.5 x 157 mm  
1x 0.8 x 4 x 157 mm  
1x 1 x 5.5 x 157 mm



**247 Single-pole phase tester, 0.5 x 3 x 70 mm**

 05005655001<sup>1)</sup> 1x 0.5 x 3 x 70 mm



<sup>1)</sup> Product not available in the USA and Canada.

Web link

Wera - Kraftform Kompakt VDE 16 Universal 1 Tool Finder  
05006607001 - 4013288229922

Wera Werkzeuge GmbH  
Korzterter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm



Product not available in the USA and Canada.

Web link

Wera - Kraftform Kompakt VDE 16 Universal 1 Tool Finder  
05006607001 - 4013288229922

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)