



<b>EAN:</b>	4013288230034	<b>Size:</b>	0x0x0 mm
<b>Part number:</b>	05006631001	<b>Weight:</b>	0 g
<b>Article number:</b>	Kraftform Kompakt VDE Stainless 17 extra slim 1 Tool Finder	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- 2 VDE-insulated Kraftform 3817 VDE bitholding screwdrivers with anti-roll protection
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication
- Blades made of stainless steel to prevent extraneous rust
- Individually tested VDE Stainless blades, some of which with reduced blade diameter
- Vacuum ice-hardening provides the required hardness and strength
- Individually tested tool as per IEC 60900 at 10,000V
- In robust pouch
- Suitable for Wera 2go

2x 3817 Kraftform VDE bitholding screwdrivers for ergonomic screwdriving. 15 VDE stainless blades, some of which with reduced blade diameter (iS), so that even low-lying screw and spring elements can be easily reached and operated; with "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. Wera's stainless steel tools are vacuum ice tempered and therefore have the hardness and strength properties required for screw connections. Industrial use is possible without restrictions. In a robust belt pouch. The pouch is suitable for attachment to walls, shelves, workshop trolleys and the Wera 2go system thanks to the hook and loop fastener system on the back.

**Web link**

Wera - Kraftform Kompakt VDE Stainless 17 extra slim 1 Tool Finder  
05006631001 - 4013288230034



**Screw stainless steel together with stainless steel!**




The Kraftform Kompakt series stands for low weight, low space requirements and high flexibility due to interchangeable blades.



Solution to the rust problem: screwdriving stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

**Individually tested**




Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

**Handle/interchangeable blade system – Kraftform Kompakt VDE**




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

**Easy exchange**




Kraftform Kompakt VDE sets come with an insulated handle and insulated inter-changeable blades, that can be exchanged without any special tools.

**Reduced blade diameter for lower-lying screws**




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

**“Take it easy” tool finder**



The Kraftform Kompakt VDE blades are equipped with the "Take it easy" Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

**Hexagonal anti-roll feature against rolling away**



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

**Web link**

Wera - Kraftform Kompakt VDE Stainless 17 extra slim 1 Tool Finder  
05006631001 - 4013288230034

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Set contents:

**3817 VDE Kraftform Stainless blade-holding handle, 9 x 98 mm**

05003991001 2x 9 x 98 mm



**Kraftform Kompakt VDE 3062 iS, stainless steel, PH 1 x 157 mm**



1x PH 1 x 157 mm

1x PH 2 x 157 mm



**Kraftform Kompakt VDE 3065 iS PZ Take it easy, stainless steel, PZ 1 x 157 mm**

1x PZ 1 x 157 mm

1x PZ 2 x 157 mm



**Kraftform Kompakt VDE 3065 iS PZ/S Take it easy, stainless steel, # 1 x 157 mm**

1x # 1 x 157 mm

1x # 2 x 157 mm



**Kraftform Kompakt VDE 3067 i TORX® Take it easy, stainless steel, TX 10 x 157 mm**

1x TX 10 x 157 mm



**Kraftform Kompakt VDE 3067 iS TORX® Take it easy, stainless steel, TX 15 x 157 mm**

1x TX 15 x 157 mm

1x TX 20 x 157 mm

1x TX 25 x 157 mm



**Kraftform Kompakt VDE 3060 i Take it easy, stainless steel, 0.4 x 2.5 x 157 mm**

1x 0.4 x 2.5 x 157 mm

1x 1.2 x 6.5 x 157 mm



**Kraftform Kompakt VDE 3060 iS Take it easy, stainless steel, 0.6 x 3.5 x 157 mm**

1x 0.6 x 3.5 x 157 mm

1x 0.8 x 4 x 157 mm

1x 1 x 5.5 x 157 mm



**Hook and Loop Fastener Strip 70, 50 x 70 mm**

1x 50 x 70 mm



Web link