



<b>EAN:</b>	4013288229977	<b>Size:</b>	0x0x0 mm
<b>Part number:</b>	05006612001	<b>Weight:</b>	0 g
<b>Article number:</b>	Kraftform Kompakt VDE 17 extra slim 1 Tool Finder	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- 2 VDE-insulated Kraftform 817 VDE blade-holding screwdrivers with anti-roll protection
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication
- Individually tested tools as per IEC 60900
- Multifunctional pliers for electrical installation: cable cutting, stripping, gripping, bending, deburring, crimping of wire end ferrules
- Pliers including cable shears with precision cutting edges (inductively hardened) for Cu and Al cables up to 5 x 2.5mm<sup>2</sup> / Ø 15 mm
- In robust pouch
- Suitable for Wera 2go

2x 817 VDE bitholding screwdrivers for Wera VDE blades; 14 VDE blades (each 157 mm length) with reduced blade diameter (items Kraftform Kompakt 60 i Take it easy 0.4x2.5 and Kraftform Kompakt 67 i Take it easy TX 10 standard blade diameter), so that even low-lying screw and spring elements can be easily reached and operated. With "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool. Individually tested tools as per IEC 60900 at 10,000 V for safe working at the approved voltage of 1,000 V. 1x Knipex VDE 13 96 200 pliers for electrical installation; these pliers replace up to 6 individual tools for electrical installation: cutting, stripping, gripping, bending, deburring and crimping - all in one tool. With safety pawl for gentle gripping. Chrome-plated for better rust protection, with insulated multi-component handle sleeves. In a robust belt pouch. The textile box features a fleece zone at the back. Using the provided self-adhesive hook and loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.

**Web link**

Wera - Kraftform Kompakt VDE 17 extra slim 1 Tool Finder  
05006612001 - 4013288229977



Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

**Individually tested**




Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

**Handle/interchangeable blade system – Kraftform Kompakt VDE**



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

**Easy change**




The Kraftform Kompakt VDE blades can be replaced simply by pulling down the yellow ring on the handle.

**PlusMinus screwdrivers**




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

**VDE interchangeable blade with reduced shaft diameter**




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

**“Take it easy”**




The Kraftform Kompakt VDE blades are equipped with the “Take it easy” Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

**Hexagonal anti-roll feature against rolling away**



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

**Fast spinning**



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.


**Web link**

Wera - Kraftform Kompakt VDE 17 extra slim 1 Tool Finder  
05006612001 - 4013288229977

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Set contents:

817 VDE Kraftform blade-holding handle, 9 x 98 mm

 05003990001 2x 9 x 98 mm



Kraftform Kompakt VDE 62 iS Take it easy, PH 1 x 157 mm

 1x PH 1 x 157 mm  
1x PH 2 x 157 mm



Kraftform Kompakt VDE 65 iS Take it easy, PZ 1 x 157 mm

 1x PZ 1 x 157 mm  
1x PZ 2 x 157 mm



Kraftform Kompakt VDE 65 iS PZ/S Take it easy, # 1 x 157 mm

 1x # 1 x 157 mm  
1x # 2 x 157 mm



Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm

 1x TX 10 x 157 mm



Kraftform Kompakt VDE 67 iS TORX® Take it easy, TX 15 x 157 mm

 1x TX 15 x 157 mm  
1x TX 20 x 157 mm  
1x TX 25 x 157 mm




Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm

 1x 0.4 x 2.5 x 157 mm



Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm

 1x 0.6 x 3.5 x 157 mm  
1x 0.8 x 4 x 157 mm  
1x 1 x 5.5 x 157 mm



Web link



1x

Hook and Loop Fastener Strip 70, 50 x 70 mm



1x 50 x 70 mm

**Web link**

Wera - Kraftform Kompakt VDE 17 extra slim 1 Tool Finder  
05006612001 - 4013288229977

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)