## PLA+ 3D Filament For 3D Printers





## **Features**

- High rigidity, good glossiness
- Suitable for printing large models
- No wiredrawing problem
- · No cracking problem

## **Specifications**

Print temperature : 205°C to 225°C

Bed temperature : 60°C to 80°C

Print speed : 30 to 90mm/s

## **Part Number Table**

Description	Colour	Part Number
PLA+ Filament, 1.75mm, 1kg/roll	Light Blue	MC011450
PLA+ Filament, 1.75mm, 1kg/roll	Dark Blue	MC011457
PLA+ Filament, 1.75mm, 1kg/roll	Light brown	MC011455
PLA+ Filament, 1.75mm, 1kg/roll	Olive Green	MC011456
PLA+ Filament, 1.75mm, 1kg/roll	Pine Green	MC011453
PLA+ Filament, 1.75mm, 1kg/roll	Peach	MC011454
PLA+ Filament, 1.75mm, 1kg/roll	Peak Green	MC011451
PLA+ Filament, 1.75mm, 1kg/roll	Purple	MC011452
PLA+ Filament, 1.75mm, 1kg/Roll	Black	MC002547
PLA+ Filament, 1.75mm, 1kg/Roll	Green	MC002548
PLA+ Filament, 1.75mm, 1kg/Roll	Grey	MC002549
PLA+ Filament, 1.75mm, 1kg/Roll	Orange	MC002550
PLA+ Filament, 1.75mm, 1kg/Roll	Red	MC002551
PLA+ Filament, 1.75mm, 1kg/Roll	Silver	MC002552
PLA+ Filament, 1.75mm, 1kg/Roll	Blue	MC002553
PLA+ Filament, 1.75mm, 1kg/Roll	White	MC002554
PLA+ Filament, 1.75mm, 1kg/Roll	Yellow	MC002555
PLA+ Filament, 1.75mm, 1kg/Roll	Gold	MC002556
PLA+ Filament, 1.75mm, 1kg/Roll	Brown	MC002557
PLA+ Filament, 1.75mm, 500g	Black	MP002267
PLA+ Filament, 1.75mm, 500g	Brown	MP002268

Description	Colour	Part Number
PLA+ Filament, 1.75mm, 500g	White	MP002269
PLA+ Filament, 1.75mm, 500g	Light Blue	MP002270
PLA+ Filament, 1.75mm, 500g	Fire Engine Red	MP002271
PLA+ Filament, 1.75mm, 500g	Green	MP002272
PLA+ Filament, 1.75mm, 500g	Grey	MP002273
PLA+ Filament, 1.75mm, 500g	Magenta	MP002274
PLA+ Filament, 1.75mm, 500g	Orange	MP002275
PLA+ Filament, 1.75mm, 500g	Pink	MP002276
PLA+ Filament, 1.75mm, 500g	Pine Green	MP002277
PLA+ Filament, 1.75mm, 500g	Red	MP002278
PLA+ Filament, 1.75mm, 500g	Silver	MP002279
PLA+ Filament, 1.75mm, 500g	Blue	MP002280
PLA+ Filament, 1.75mm, 500g	Peak Green	MP002281
PLA+ Filament, 1.75mm, 500g	Yellow	MP002282
PLA+ Filament, 1.75mm, 500g	Purple	MP002283
PLA+ Filament, 1.75mm, 500g	Bone White	MP002284
PLA+ Filament, 1.75mm, 500g	Light Brown	MP002285
PLA+ Filament, 1.75mm, 500g	Olive Green	MP002286
PLA+ Filament, 1.75mm, 500g	Dark Blue	MP002287

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Page <1> 19/08/24 V1.3