



GWAVRD

Mini Wireless Screen Sharing with HDMI® Connection

Ditch the cables and mirror your world wirelessly! The IOGEAR GWAVRD is your ticket to hassle-free screen sharing. This compact adapter connects to your TV, projector, or monitor, letting you stream content from your laptop, phone, or tablet in Full HD 1080p.



HDMI®
HIGH DEFINITION MULTIMEDIA INTERFACE



Features

- Wirelessly mirror small screen from your laptop or phone to a big display screen or projector.
- Maximum resolutions of 1080p @60Hz.
- Wireless 2.4/5 GHz with WPA-2 security.
- Low latency
- Range up to 30 Ft. in-room only.
- Design so compact you can carry it in your pocket
- OS compatibility: Windows 10[®]+, Mac[®] OS 10.14+, iOS[®] 10.10+ and Android[™] 10+, Chromebook[™]

Requirements

- Windows 10 or later.
- Mac OS 10.14 and later with computer using Metal support graphics adapter.
- iPad iOS 10.10 and above.
- iPhone iOS 10.10 and above.
- Android Smart phones 10 and above.
- Google Chromebook.
- HDTV or Projector with HDMI port.

Package Contents

- 1 x GWAVRD
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GWAVRD	DIMENSIONS	GWAVRD
Housing		POP Information	
Case	Plastic	10" Peg Hook	7
Video connections		Unit Dimensions	
Output	HDMI 1.4	Height	0.375"
Frequency Band	2.4/5 GHz	Length	28"
Video Resolution	1080p @60Hz	Depth	0.75"
Audio		Inner Pack	
Audio Output	2-Channel 16-bit AAC	Height	7"
Sample Rate	48KHz, 16-bit from HDMI connector	Width	7.75"
Antenna Type	Internal board type	Depth	4.75"
Operating Range	Up to 30 feet (9 m)	Inner Pack Qty.	6
Operating System Requirements		Unit Package Dimensions	
Windows	Windows 8.1, Windows 10	Height	5.25"
Android	Android 10+	Width	4.125"
Mac	AirPlay	Depth	1.375"
iOS	Screen Mirroring	Master Carton	
Environment		Height	8.50"
Operation Temperature	32~104°F (0~40°C)	Width	21"
Storage Temperature	14~158°F (-10~70°C)	Depth	9.25"
Warranty	1-Year	Master Carton Qty.	24
Humidity	10% to 85% RH (Non condensing)	Weight	
Voltage	5V/0.5A	Master Carton Wt.	8.77 lb
		Inner Pack Wt.	1.36 lb
		Unit Pack Wt.	0.22 lb
		Unit Wt.	0.05 lb