



EAN:	4013288229991	Size:	202x80x82 mm
Part number:	05006613001	Weight:	676 g
Article number:	Kraftform Kompakt VDE 18 Universal 1 Tool Finder	Country of origin:	CZ
		Customs tariff number:	82054000



- VDE-insulated Kraftform 817 VDE bitholding screwdriver with anti-roll protection
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication
- Individually tested tools as per IEC 60900
- In robust pouch
- Suitable for Wera 2go

One 817 VDE Kraftform bitholding screwdriver, 12 VDE blades with "Take it easy" Tool finder: Colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool, 4 control cabinet keys, one single-pole phase tester. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. In a robust belt pouch. The textile box features a fleece zone at the back. Using the provided self-adhesive hook and loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.

Web link

Wera - Kraftform Kompakt VDE 18 Universal 1 Tool Finder
05006613001 - 4013288229991

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Individually tested



Why is the right tool so often missing at the workplace? The reason: too many tools and overly-heavy tool bags can make it bothersome to carry keep them with you. So for us it was a clear challenge: to develop a tool that is suitable for a whole host of applications and can be easily taken along to the workplace. Our solution: Kraftform Kompakt tools. A handle into which blades with a range of different profiles can be inserted. Compactly and protectively housed in a light and robust textile pouch - and they are even VDE-tested, too.




Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

Handle/interchangeable blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Easy change




The Kraftform Kompakt VDE blades can be replaced simply by pulling down the yellow ring on the handle.

“Take it easy”




The Kraftform Kompakt VDE blades are equipped with the "Take it easy" Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

Fast spinning



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.

Belt pouch



Storage and transport in a robust textile pouch, so the tool is well protected and always close at hand.


Web link

Wera - Kraftform Kompakt VDE 18 Universal 1 Tool Finder
05006613001 - 4013288229991

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

817 VDE Kraftform blade-holding handle, 9 x 98 mm

 05003990001 1x 9 x 98 mm




Kraftform Kompakt VDE 62 i Take it easy, PH 1 x 157 mm

 1x PH 1 x 157 mm
1x PH 2 x 157 mm



Kraftform Kompakt VDE 65 i Take it easy, PZ 1 x 157 mm

 1x PZ 1 x 157 mm
1x PZ 2 x 157 mm




Kraftform Kompakt VDE 62 i PH/S Take it easy, # 1 x 157 mm

 1x # 1 x 157 mm
1x # 2 x 157 mm




Kraftform Kompakt VDE 65 i PZ/S Take it easy, # 1 x 157 mm

 1x # 1 x 157 mm
1x # 2 x 157 mm




Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm

 1x 0.4 x 2.5 x 157 mm
1x 0.6 x 3.5 x 157 mm
1x 0.8 x 4 x 157 mm
1x 1 x 5.5 x 157 mm




Kraftform Kompakt 96 VK 6,3, 6.3 x 89 mm

 05003460001 1x 6.3 x 89 mm



Kraftform Kompakt 97 VK 8,1, 8.1 x 89 mm

 05003461001 1x 8.1 x 89 mm



Web link

Kraftform Kompakt 98 DK, 89 mm



05003462001

1x 89 mm



Kraftform Kompakt 99 FL, 89 mm



05003463001

1x 89 mm



247 Single-pole phase tester, 0.5 x 3 x 70 mm



05005655001¹⁾


1x 0.5 x 3 x 70 mm



1) Product not available in the USA and Canada.

Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm



Product not available in the USA and Canada.

Web link

Wera - Kraftform Kompakt VDE 18 Universal 1 Tool Finder
05006613001 - 4013288229991

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de