

Surface-mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)


HCV88880000SB000

Hi-Cap X7R Series Sample Kit

Spec Sheet

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for General Electronic equipments .



No.	Part. NO.	Size	TC	Cap.	Volt.	Tol	No.	Part. NO.	Size	TC	Cap.	Volt.	Tol
1	CC0402KRX7R5BB105	0402	X7R	1µF	6.3V	±10%	30	CC1206KKX7R7BB105	1206	X7R	1µF	16V	±10%
2	CC0402KRX7R6BB105	0402	X7R	1µF	10V	±10%	31	CC1206KKX7R7BB225	1206	X7R	2.2µF	16V	±10%
3	CC0402MRX7R5BB225	0402	X7R	2.2µF	6.3V	±20%	32	CC1206KKX7R7BB475	1206	X7R	4.7µF	16V	±10%
4	CC0402KRX7R5BB225	0402	X7R	2.2µF	6.3V	±10%	33	CC1206KKX7R7BB106	1206	X7R	10µF	16V	±10%
5	CC0603MRX7R5BB475	0603	X7R	4.7µF	6.3V	±20%	34	CC1206KKX7R8BB105	1206	X7R	1µF	25V	±10%
6	CC0603KRX7R6BB225	0603	X7R	2.2µF	10V	±10%	35	CC1206KKX7R8BB225	1206	X7R	2.2µF	25V	±10%
7	CC0603KRX7R7BB105	0603	X7R	1µF	16V	±10%	36	CC1206KKX7R8BB475	1206	X7R	4.7µF	25V	±10%
8	CC0603KRX7R7BB225	0603	X7R	2.2µF	16V	±10%	37	CC1206KKX7R8BB106	1206	X7R	10µF	25V	±10%
9	CC0603KRX7R8BB105	0603	X7R	1µF	25V	±10%	38	CC1206KKX7R8BB106	1206	X7R	10µF	35V	±10%
10	CC0603KRX7R9BB105	0603	X7R	1µF	50V	±10%	39	CC1206KKX7R9BB105	1206	X7R	1µF	50V	±10%
11	CC0805KKX7R5BB106	0805	X7R	10µF	6.3V	±10%	40	CC1206KKX7R9BB225	1206	X7R	2.2µF	50V	±10%
12	CC0805KKX7R6BB105	0805	X7R	1µF	10V	±10%	41	CC1206KKX7R9BB475	1206	X7R	4.7µF	50V	±10%
13	CC0805KKX7R6BB225	0805	X7R	2.2µF	10V	±10%	42	CC1206KKX7R0BB105	1206	X7R	1µF	100V	±10%
14	CC0805KKX7R6BB475	0805	X7R	4.7µF	10V	±10%	43	CC1206KKX7R0BB225	1206	X7R	2.2µF	100V	±10%
15	CC0805KKX7R6BB106	0805	X7R	10µF	10V	±10%	44	CC1210KKX7R6BB226	1210	X7R	22µF	10V	±10%
16	CC0805KKX7R7BB105	0805	X7R	1µF	16V	±10%	45	CC1210KKX7R7BB475	1210	X7R	4.7µF	16V	±10%
17	CC0805KKX7R7BB225	0805	X7R	2.2µF	16V	±10%	46	CC1210KKX7R7BB106	1210	X7R	10µF	16V	±10%
18	CC0805KKX7R7BB475	0805	X7R	4.7µF	16V	±10%	47	CC1210KKX7R7BB226	1210	X7R	22µF	16V	±10%
19	CC0805MKX7R7BB106	0805	X7R	10µF	16V	±20%	48	CC1210KKX7R8BB105	1210	X7R	1µF	25V	±10%
20	CC0805KKX7R8BB105	0805	X7R	1µF	25V	±10%	49	CC1210KKX7R8BB225	1210	X7R	2.2µF	25V	±10%
21	CC0805KKX7R8BB225	0805	X7R	2.2µF	25V	±10%	50	CC1210KKX7R8BB475	1210	X7R	4.7µF	25V	±10%
22	CC0805KKX7R8BB475	0805	X7R	4.7µF	25V	±10%	51	CC1210KKX7R8BB106	1210	X7R	10µF	25V	±10%
23	CC0805KKX7R9BB105	0805	X7R	1µF	50V	±10%	52	CC1210KKX7R8BB226	1210	X7R	22µF	25V	±10%
24	CC0805KKX7R9BB225	0805	X7R	2.2µF	50V	±10%	53	CC1210KKX7R9BB105	1210	X7R	1µF	50V	±10%
25	CC0805KKX7R0BB105	0805	X7R	1µF	100V	±10%	54	CC1210KKX7R9BB225	1210	X7R	2.2µF	50V	±10%
26	CC1206KKX7R6BB225	1206	X7R	2.2µF	10V	±10%	55	CC1210KKX7R9BB475	1210	X7R	4.7µF	50V	±10%
27	CC1206KKX7R6BB475	1206	X7R	4.7µF	10V	±10%	56	CC1210KKX7R9BB106	1210	X7R	10µF	50V	±10%
28	CC1206KKX7R6BB106	1206	X7R	10µF	10V	±10%	57	CC1210KKX7R0BB105	1210	X7R	1µF	100V	±10%
29	CC1206KKX7R6BB226	1206	X7R	22µF	10V	±10%	58	CC1210KKX7R0BB225	1210	X7R	2.2µF	100V	±10%

Piecs per items: Case size 01005 to 0402, 80pcs; 0603 to 1808, 40pcs; 1812, 20pcs.