

DEUTSCH | DEUTSCH HD, DEUTSCH HD30

TE Internal #: 114017-ZZ

Cavity Plug, PBT, White, -55 – 125 °C [-67 – 257 °F] Operating

Temperature, DEUTSCH HD30

View on TE.com >



Connectors > Connector Accessories > Connector Seals & Cavity Plugs > DEUTSCH Sealing Plugs











Connector Seal & Plug Type: Cavity Plug

Primary Product Material: **PBT**Primary Product Color: **White**

Resistance to Hydrocarbons: Good

Operating Temperature (Max): 125 °C [257 °F]

All DEUTSCH Sealing Plugs (10)

Features

Product Type Features

| Connector Seal & Plug Type | Cavity Plug |
|-----------------------------|----------------------------|
| Body Features | |
| Primary Product Material | PBT |
| Primary Product Color | White |
| Usage Conditions | |
| Operating Temperature (Max) | 125 °C[257 °F] |
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |
| Industry Standards | |
| UL Flammability Rating | UL 94V-0 |
| Packaging Features | |
| Packaging Quantity | 1 |
| Packaging Method | Box |



Other

| Resistance to Hydrocarbons | Good |
|----------------------------|------|
| Contains Lubricant | No |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU | Compliant |
|---|---|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts













TE Part # CAT-D799-CH8172 DEUTSCH DRC Housings



TE Part # CAT-D781-CH8172 DEUTSCH DRB Housings



TE Part # CAT-H3910-CH8172 DEUTSCH HD10 Housings



TE Part # CAT-D486-CH8172 DEUTSCH DTP Housings



TE Part # CAT-ST858-CH8172 DEUTSCH Strike Housings



TE Part # CAT-D48-PCH8172 DEUTSCH DTHD Housings



TE Part # CAT-J41-DDCC **DEUTSCH DT Color Connectors**



TE Part # DRCP28-86SB PLG, 86P, BLK, 12/20, B



TE Part # DRCP28-86SC PLG, 86P, BLK, 12/20, C



TE Part # CAT-D487-CH8172 DEUTSCH DT Series Housings & Connectors



TE Part # HD10-9-96P-N005 SQ FG REC ASM



TE Part # HDFB-16-06S MODULE, FEEDBACK, 21P, GRAY, SZ16, SOC



TE Part # DTV06-18SC PLG, 18P, GRN, N, C



TE Part # DTV06-18SA PLG, 18P, GRY, N, A



TE Part # DTV06-18SB PLG, 18P, BLK, N, B



TE Part # DTV02-18PA REC, 18P, GRY, N, FLANGE, A

Also in the Series | DEUTSCH HD



Automotive Connector Caps & Covers (32)



Automotive Housings(768)



Connector Backshells(29)



Connector Seals & Cavity Plugs(10)






Connector Strain Relief(5)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(11)



PCB Headers & Receptacles(1)

Also in the Series | DEUTSCH HD30



Automotive Connector Caps & Covers (14)



Automotive Housings(359)



Connector Backshells(2)



Connector Seals & Cavity Plugs(11)



Connector Strain Relief(5)



Insertion & Extraction Tools(10)



Other Automotive Connector Accessories(6)

Customers Also Bought







Documents

Product Drawings SEALING PLUG, SIZE 12/16, WHT

English

CAD Files 3D PDF



3D

Customer View Model

ENG_CVM_CVM_114017-ZZ_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_114017-ZZ_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_114017-ZZ_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English