



[Request Free Catalogue](#)

 You are here: [Home](#) ▶ [Cable Ties and Cable Management](#) ▶ [Aluminium Clamp /Aluminium Clamp with Vinyl Coating](#)

[New Products](#)
[All Series](#)
[Cable Ties and Cable Management](#)
[Caps and Plugs](#)
[Card Guides and Pullers](#)
[Circuit Board Hardware](#)
[EMI Suppression Ferrite Cores](#)
[Fan Accessories](#)
[Fasteners and Fixings](#)
[Feet](#)
[Fibre Management](#)
[Furniture Fittings](#)
[Gasketing, Toggle Clamps and Enclosure Accessories](#)
[Handles, Knobs and Positioning Components](#)
[High Temperature Masking](#)
[Hydraulic and Pneumatic](#)

## Aluminium Clamp /Aluminium Clamp with Vinyl Coating



Aluminium clamp/Aluminium clamp with vinyl coating is supplied in aluminium alloy 5052 H-32 RMS-199 or aluminium alloy 5052 H-32, RMS-199 with black PVC RMS-118 coating. It is a suitable clamping component that can be applied for low or high voltage cable management requirements. We supply this component in various "D" holding diameters.

### Applications and Benefits of Aluminium Clamp/Aluminium Clamp with Vinyl Coating

- It is supplied in aluminium alloy 5052 H-32 RMS-199 or aluminium alloy 5052 H-32, RMS-199 with black PVC RMS-118 coating.
- Suitable clamping component for low or high voltage cable management purposes.
- Available in different "D" holding diameters to suit varying cable sizes and thicknesses.

[Request Sample](#)
[Convert to Inches](#)
[Add to Cart](#)

 Showing 1 to 28 of 28 entries Show  entries

&lt;&lt;&lt;1&gt;&gt;&gt;

 Search:

- Protection Essentra

---

- LED Hardware

---

- Locks, Latches, Catches and Hinges

---

- Pipe and Flange Protection Essentra

---

- Tube Inserts, Connectors and Ferrules

---

- Vibration Mounts and Slide Bearings

---

## Cart

Your cart is empty

## Sample Request

No Sample request in cart

## News

Sample	Part Number	Material	"D" Holding Ø (mm)	"E" (mm)	"T" (mm)	"W" (mm)	Unit of Measurements	Price (Ex. GST)	Quantity	Total
<input type="checkbox"/>	AL10	Aluminum Alloy, 5052 H-32, RMS-199	15.9	19.8	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL11	Aluminum Alloy, 5052 H-32, RMS-199	17.5	20.6	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL12	Aluminum Alloy, 5052 H-32, RMS-199	19.1	21.3	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL14	Aluminum Alloy, 5052 H-32, RMS-199	22.2	22.9	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL16	Aluminum Alloy, 5052 H-32, RMS-199	25.4	24.4	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL18	Aluminum Alloy, 5052 H-32, RMS-199	28.6	26.7	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL2	Aluminum Alloy, 5052 H-32, RMS-199	3.2	11.7	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input checked="" type="checkbox"/>	AL3	Aluminum Alloy, 5052 H-32, RMS-199	4.8	12.7	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL4	Aluminum Alloy, 5052 H-32, RMS-199	6.4	13.5	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL5	Aluminum Alloy, 5052 H-32, RMS-199	7.9	14.2	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	

Sample	Part Number	Material	"D" Holding Ø (mm)	"E" (mm)	"T" (mm)	"W" (mm)	Unit of Measurements	Price (Ex. GST)	Quantity	Total
<input type="checkbox"/>	AL6	Aluminum Alloy, 5052 H- 32, RMS-199	9.5	15	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL7	Aluminum Alloy, 5052 H- 32, RMS-199	11.1	15.7	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL8	Aluminum Alloy, 5052 H- 32, RMS-199	12.7	16.5	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	AL9	Aluminum Alloy, 5052 H- 32, RMS-199	14.3	19.1	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE10	Aluminum Alloy, 5052 H- 32, RMS-199, Coating: Black PVC, RMS-118	15.9	19.8	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE11	Aluminum Alloy, 5052 H- 32, RMS-199, Coating: Black PVC, RMS-118	17.5	20.6	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE12	Aluminum Alloy, 5052 H- 32, RMS-199, Coating: Black PVC, RMS-118	19.1	21.3	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE14	Aluminum Alloy, 5052 H- 32, RMS-199,	22.2	22.9	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	

Sample	Part Number	Material	"D" Holding Ø (mm)	"E" (mm)	"T" (mm)	"W" (mm)	Unit of Measurements	Price (Ex. GST)	Quantity	Total
<input type="checkbox"/>	NE16	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	25.4	24.4	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE18	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	28.6	26.7	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE20	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	31.8	28.2	1.6	12.7	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE3	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	4.8	12.7	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE4	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	6.4	13.5	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE5	Aluminum Alloy, 5052 H- 32, RMS-199,	7.9	14.2	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	

Sample	Part Number	Material	"D" Holding Ø (mm)	"E" (mm)	"T" (mm)	"W" (mm)	Unit of Measurements	Price (Ex. GST)	Quantity	Total
<input type="checkbox"/>	NE6	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	9.5	15	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE7	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	11.1	15.7	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE8	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	12.7	16.5	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	
<input type="checkbox"/>	NE9	Coating: Black PVC, RMS-118 Aluminum Alloy, 5052 H- 32, RMS-199,	14.3	19.1	0.8	9.5	- Bag o ▼	0.00 Rs	<input type="text" value="0"/>	

Showing 1 to 28 of 28 entries

Show  ▼ entries

<<<1>>>

Search:

Request Sample


Need Help

Add to Cart

## Quick Links



Tapered Caps and Plugs



Spiralguard



High Temperature Plugs



Metal Threaded Insert



Feet



Castors



Hinges



Locks



Handles



Securing Solutions



Cable Ties



Cable Gland



Fastener

ESSENTIAL SOLUTIONS

DELIVERED

Adhesive Tapes And Pads  
 Airflute Sheeting  
 Caps and Plugs  
 Card Guides and Pullers  
 Castors

Circuit Board Hardware  
 Fan Accessories  
 Fasteners and Fixings  
 Feet  
 Fibre Management

Flange Protectors  
 Furniture Fittings  
 Industrial Wipes  
 LED Hardware  
 Oilfield Tool Joint Protectors

Pipe & Tube Caps  
 Plastic Fence Feet Blocks  
 Securing Solutions  
 Sleeve Web/Netting  
 Spiral Guard



[Privacy Policy](#) | [Health, Safety and Environment Policy Statement](#) | [Sustainability](#) | [Modern Slavery Statement](#)  
 Copyright © 2024 Essentra (India) Private Limited - All Rights Reserved.