

**RoHS  
Compliant**



## Features

- True RMS
- Data hold/backlight
- Max/Min/Relative mode
- USB communication
- Input protection and Diode/continuity test
- NCV (audible/visual alarm)

## Electrical Specifications

Certifications	CE	
Safety Ratings	CAT III 1000V/CAT IV 600V	
AC voltage (V)	1000V	±(1% +3)
DC voltage (V)	1000V	±(0.5% +3)
AC current (A)	10A	±(1.2% +5)
DC current (A)	10A	±(1% +2)
Resistance (Ω)	60MΩ	±(1% +2)
Capacitance (F)	60mF	±(3% +5)
Frequency (Hz)	10MHz	±(0.1% +4)
Duty cycle (%)	0.1% to 99.9%	±(2% +5)
Display count	6000	
Bandwidth (Hz)	40Hz to 500Hz	
Analog bar	31	

## General Characteristics

Power	: 1.5V Battery (R03) × 4
Product Net Weight	: 350g
Product Size	: 190mm × 90mm × 50mm
Standard Warranty	: 12 Months

Accessories	Qty.	Note
Operating Manual	1 piece	-
Test Leads	1 pair	UL 18AWG(E331984) Double insulated cable length 1.2m CAT III 1000V/CAT IV 600V 10A
Battery	4 pieces	1.5V AAA × 4, Replaceable
Cloth bag	1 piece	-

## Part Number Table

Description	Part Number
Hand Held Digital Multimeter, 1000V AC/DC, 10A AC/DC, 60MΩ, 60mF, 10MHz	MP730651

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp<sup>PRO</sup>**