



GUD3C8K2P

USB-C 8K Nano Dock Pro

IOGEAR's USB-C 8K Nano Dock Pro expands the connectivity of your laptop or tablet's USB-C port. Travel lighter with this portable, 6-in-1 dock and leave your bulky accessories at home. The Dock is equipped with a USB-C power charging pass-through port, three USB-A expansion ports and 2 HDMI ports.



Features

- 6-in-1 Travel-size USB-C docking station for mobile professionals
- Charge laptop & devices with up to 100W pass-through*
- Up to 8K in single display mode or up to 4K in dual display mode
- 13" inch cable
- 1x USB-A 3.0 ports; 2x USB-A 2.0 ports
- Compatible with Thunderbolt 3/4 (USB-C) laptops & tablets
- Rugged aluminum housing
- Works with the new USB-C iPad Pro under mirror-mode

* Maximum of up to 85W of power can be delivered to the laptop after deduction of 15W used by the docking station. Pass-thru power delivered to the laptop is dependent upon the capacity of your USB-C power supply. Ex. If your USB-C power supply is 60W, then the maximum power can be delivered to the laptop is $60W - 15W = 45W$. If your power supply is 87W, then the maximum power can be delivered to the laptop is $87W - 15W = 72W$.

Requirements

- USB-C compatible laptops with DP Alt-Mode support
- USB-C AC Adapter from Laptop is needed for Power Delivery Pass-Through Function
- Compatible with USB-C and Thunderbolt 3/4 laptops
- OS Support
 - Windows 10,11
 - macOS 13+ (MST is not supported by Mac OS)
 - iPadOS 15+

Package Contents

- 1x GUD3C8K2P
- 1x QSG
- 1x Warranty Card



Specifications

FUNCTION	GUD3C8K2P	DIMENSIONS	GUD3C8K2P
Cable Length	13" (33 cm)	Unit Dimensions	
Cable Connections		Height	0.5" (1.3 cm)
Input	USB-C Host	Length	Base: 3.9" (10.1 cm) Cable: 13" (33 cm)
Connectors		Width	1.5" in (4 cm)
Power	USB-C PD 3.0 up to 100W	Inner Pack	
USB-A	2x USB 2.0, 1x USB 3.0 (5Gbps)	Height	4.5" (11.6 cm)
Video Output	1x HDMI (8K @ 30Hz) 1x HDMI (4K @ 30Hz)	Length	9.64" (24.5 cm)
		Width	6.2" (16 cm)
		Inner Pack Qty.	6 pcs
		Unit Package Dimensions	
		Height	3" (7.62 cm)
		Length	6" (15.24 cm)
		Width	2" (5.08 cm)
		Master Carton	
		Height	10" (25.5 cm)
		Length	13.3" (34 cm)
		Width	10.4" (26.5 cm)
		Master Carton Qty.	24 pcs
		Weight	
		Master Carton Wt.	9.5 lbs (4.32 kgs)
		Inner Pack Wt.	2.15 lbs (0.98 kgs)
		Unit Pack Wt.	0.3 lbs (0.12 kgs)
		Unit Wt.	0.15 lbs (0.08 kg)