



GWAVR4K

Mini Wireless 4K HDMI® Screen Sharing Adapter

Cut the cords and cast your content onto the big screen! Introducing the IOGEAR GWAVR4K, a mini wireless adapter that unlocks the magic of 4K screen sharing. Ditch the tangled wires and enjoy seamless streaming of movies, photos, presentations, and more – all in stunning 4K resolution – from your phone, laptop, or tablet to any HDMI-equipped display.



Features

- Wirelessly cast content from your phone/tablet/PC to a large display screen or projector
- Maximum resolution of 4K @30Hz
- Wireless 2.4/5GHz with WPA-2 security
- Low screen casting latency
- Range up to 30 ft. in-room only
- Compact and lightweight design
- OS compatibility: Windows 10[®]+, Mac[®] OS 10.14+, iOS[®] 10.10+ and Android[™] 10+, Chromebook[™]
- Turn an old TV (HDMI[®] enabled) into a smart TV

Requirements

Display:

- 1x HDMI Port

OS Requirements:

- Windows 10 or later.
- Mac OS 10.14 and later
- iPad iOS 10.10 and above.
- iPhone iOS 10.10 and above.
- Android Smart phones 10 and above.

Package Contents

- 1 x GWAVR4K
- 1 x USB Power Cable with Antenna
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GWAVR4K	DIMENSIONS	GWAVR4K
Housing		POP Information	
Case	Plastic	10" Peg Hook	7
Video connections		Unit Dimensions	
Output	HDMI 1.4	Height	0.35"
Frequency Band	2.4/5 GHz	Length	42.50"
Video Resolution	Output up to 4K @30Hz	Width	1.10"
Audio		Inner Pack	
Audio Output	2-Channel 16-bit AAC	Height	7.125"
Sample Rate	48 kHz 16-bit from HDMI connector	Length	7.875"
Antenna Type	Board type integrated with power cable	Width	4.75"
Operating Range	30 ft.(9 m)	Inner Pack Qty.	6
Operating System Requirements		Unit Package Dimensions	
Windows	10 or later	Height	5.25"
Android	10 or later	Length	4.125"
Mac	Airplay	Width	1.375"
iOS	Screen Mirroring	Master Carton	
Operating Temperature	32~104°F (0~40°C)	Height	8.50"
Environment		Length	21"
Storage Temperature	14~158°F (-10~70°C)	Width	9.25"
Humidity	10% to 85% RH (Non condensing)	Master Carton Qty.	24
Power		Weight	
Voltage	5V/0.5A	Master Carton Wt.	7.15 lb
		Inner Pack Wt.	1.45 lb
		Unit Pack Wt.	0.20 lb
		Unit Wt.	0.15 lb