

Surface-mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)


HC6666000000SB000

Hi-Cap X6S Series Sample Kit

Spec Sheet

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for General Electronic equipments .



No.	Part. NO.	Size	TC	Cap.	Volt.	Tol	No.	Part. NO.	Size	TC	Cap.	Volt.	Tol
1	CC0201MRX6S5BB105	0201	X6S	1μF	6.3V	±20%	12	CC0603MRX6S4BB106	0603	X6S	10μF	4V	±20%
2	CC0402KRX6S5BB105	0402	X6S	1μF	6.3V	±10%	13	CC0603MRX6S5BB106	0603	X6S	10μF	6.3V	±20%
3	CC0402KRX6S6BB105	0402	X6S	1μF	10V	±10%	14	CC0603MRX6S5BB226	0603	X6S	22μF	6.3V	±20%
4	CC0402KRX6S7BB105	0402	X6S	1μF	16V	±10%	15	CC0805KKX6S5BB106	0805	X6S	10μF	6.3V	±10%
5	CC0402KRX6S8BB105	0402	X6S	1μF	25V	±10%	16	CC0805KKX6S6BB106	0805	X6S	10μF	10V	±10%
6	CC0402KRX6S5BB225	0402	X6S	2.2μF	6.3V	±10%	17	CC0805KKX6S7BB106	0805	X6S	10μF	16V	±10%
7	CC0402KRX6S6BB225	0402	X6S	2.2μF	10V	±10%	18	CC0805KKX6S8BB106	0805	X6S	10μF	25V	±10%
8	CC0402MRX6S7BB225	0402	X6S	2.2μF	16V	±20%	19	CC0805MKX6S5BB226	0805	X6S	22μF	6.3V	±20%
9	CC0402MRX6S5BB475	0402	X6S	4.7μF	6.3V	±20%	20	CC0805MKX6S6BB226	0805	X6S	22μF	10V	±20%
10	CC0603KRX6S7BB225	0603	X6S	2.2μF	16V	±10%	21	CC0805MKX6S4BB476	0805	X6S	47μF	4V	±20%
11	CC0603KRX6S5BB475	0603	X6S	4.7μF	6.3V	±10%	22	CC0805MKX6S5BB476	0805	X6S	47μF	6.3V	±20%

Piecs per items: Case size 01005 to 0402, 80pcs; 0603 to 1808, 40pcs; 1812, 20pcs.