

Kraftform XXL 3, 11 pieces

Kraftform Plus – Series 300



EAN: 4013288182388
Part number: 05347106001
Article number: Kraftform XXL 3

Size: 198x285x80 mm
Weight: 1208 g
Country of origin: CZ
Customs tariff number: 82054000

- For every application the right tool
- Multi-component Kraftform handle for high working speeds and ergonomic screwdriving
- "Take it easy" tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Lasertip for more secure fit in the screw head

11-piece all-round screwdriver set. Kraftform Plus handle for pleasant, ergonomic working that prevents blisters and calluses. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Partially with Lasertip: The tips of the Wera Lasertip screwdrivers are microscopically roughened by laser beams. This rough surface literally bites into the head of the screw. Any unintentional slipping out is therefore a thing of the past. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_xxl_3.html

Wera - Kraftform XXL 3
05347106001 - 4013288182388

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series 900 – the Chiseldriver



Kraftform Plus screwdrivers - ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



The chiseldriver is the solution for jobs that require more than just screwdriving. For fastening, chiselling and loosening seized screws or hose clamps. With an integrated impact cap that extends service life and reduces the risk of splintering. With a pound-thru hexagon blade made from high-grade material for - zero-loss transfer of high forces when struck with a hammer. The tough viscous tempered material prevents the blade from splintering or breaking. More TORQUE can be transferred by attaching an open-jawed or ring spanner to the integrated hexagon bolster.

Kraftform Plus – Series 100 VDE



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Kraftform Screwdrivers Series 300



Kraftform Plus screwdrivers - ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_xxl_3.html

Wera - Kraftform XXL 3
05347106001 - 4013288182388

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Lasertip prevents slipping out




It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.

Kraftform



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

Web link



https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_xxl_3.html

Wera - Kraftform XXL 3
05347106001 - 4013288182388



Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

932 A Screwdriver for slotted screws, 1 x 5.5 x 100 mm

	05018264001	1x	1 x 5.5 x 100 mm
	05018266001	1x	1.2 x 7 x 125 mm



350 PH Screwdriver for Phillips screws, PH 1 x 80 mm

	05008710001	1x	PH 1 x 80 mm
	05008720001	1x	PH 2 x 100 mm



334 Screwdriver for slotted screws, 1.2 x 6.5 x 150 mm

	05110010001	1x	1.2 x 6.5 x 150 mm
			



335 Screwdriver for slotted screws, 0.8 x 4 x 100 mm

	05110004001	1x	0.8 x 4 x 100 mm
	05110007001	1x	1 x 5.5 x 125 mm

368 Screwdriver for square socket head screws, # 1 x 80 mm

	05117682001	1x	# 1 x 80 mm
	05117684001	1x	# 2 x 100 mm

160 i VDE Insulated screwdriver for slotted screws, 0.4 x 2.5 x 80 mm

	05006100001 ¹⁾	1x	0.4 x 2.5 x 80 mm
	05006110001 ¹⁾	1x	0.6 x 3.5 x 100 mm

1) without Lasertip

Rack for Kraftform screwdrivers, 190 x 50 mm

	05134001001	2x	190 x 50 mm
--	-------------	----	-------------



Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_xxl_3.html

Wera - Kraftform XXL 3
05347106001 - 4013288182388

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de