

Multicolour Tower Light

multicompPRO

**RoHS
Compliant**



Features

- Preassembled & Prewired Light Tower
- 70mm Diameter
- 24V AC/DC & 240V AC versions
- Super bright multi chip LED technology
- Steady Light or Multi-function Light
- Multi-function: Steady, 1 flash, 2 flash & strobe
- Available with Sounder module
- IP66 ingress protection
- Continuously rated
- -30 to +50°C Operating temperature
- High impact & self extinguishing PC body

Part Number Table

Description	Part Number
Multicolour Tower Light, Steady Red, Green, 24V AC/DC, 70mm Dia	MP014824
Multicolour Tower Light, Steady Red, Amber, Green, 24V AC/DC, 70mm Dia	MP014825
Multicolour Tower Light, Steady Red, Green With Sounder, 24V AC/DC, 70mm Dia	MP014826
Multicolour Tower Light, Steady Red, Amber, Green With Sounder, 24V AC/DC, 70mm Dia	MP014827
Multicolour Tower Light, Steady Red, Green, 240V AC, 70mm Dia	MP014828
Multicolour Tower Light, Steady Red, Amber, Green, 240V AC, 70mm Dia	MP014829
Multicolour Tower Light, Steady Red, Green With Sounder, 240V AC, 70mm Dia	MP014830
Multicolour Tower Light, Steady Red, Amber, Green With Sounder, 240 AC/DC, 70mm Dia	MP014831
Multicolour Tower Light, Multifunction Red, Green, 24V AC/DC, 70mm Dia	MP014832
Multicolour Tower Light, Multifunction Red, Amber, Green, 24V AC/DC, 70mm Dia	MP014833
Multicolour Tower Light, Multifunction Red, Green With Sounder, 24V AC/DC, 70mm Dia	MP014834
Multicolour Tower Light, Multifunction Red, Amber, Green With Sounder, 24V AC/DC, 70mm Dia	MP014835
Multicolour Tower Light, Multifunction Red, Green, 240V AC, 70mm Dia	MP014836
Multicolour Tower Light, Multifunction Red, Amber, Green, 240V AC, 70mm Dia	MP014837
Multicolour Tower Light, Multifunction Red, Green With Sounder, 240V AC, 70mm Dia	MP014838
Multicolour Tower Light, Multifunction Red, Amber, Green With Sounder, 240V AC/DC, 70mm Dia	MP014839

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO