

PBPA / PBPS PANELS

for more information visit


www.hammondmfg.com

Data subject to change without notice

PART No. PBPA & PBPS19003BK2


PBPA MATERIAL: 0.125" THK ALUMINUM

PBPS MATERIAL: 14 GA. STEEL








Aluminum Rack Panels (PBPA Series)

















Path: [Home](#) > [Rack Index](#) > Aluminum Rack Panels (PBPA)



















Features:


- 0.125" thick, easy to machine aluminum...
- Standard 19" rack panels...
- Painted versions are finished in powder paint...
- Smooth paint finish for easy labelling...
- Unfinished version is white paper covered on one side to protect finish - also used as a surface for a machining template (see photo below)...
- Standard rack mount punching on both ends...
- Requires mounting [hardware](#)

Part Number	Color	Reader File	 Drawing File Size	AutoCAD .dxf File	.dxf File Size	Panel Height		No. of Slots
						Inches	Units	
PBPA19001BK2 PBPA19001CG2 PBPA19001GY2 PBPA19001UNF	Black Gray/Beige ASA 61 Gray Unfinished		13K		74K	1.75	1	4
PBPA19003BK2 PBPA19003CG2 PBPA19003GY2 PBPA19003UNF	Black Gray/Beige ASA 61 Gray Unfinished		13K		74K	3.50	2	4

PBPA19005BK2	Black		13K		74K	5.25	3	4
PBPA19005CG2	Gray/Beige							
PBPA19005GY2	ASA 61 Gray							
PBPA19005UNF	Unfinished							
PBPA19007BK2	Black		13K		74K	7.00	4	4
PBPA19007CG2	Gray/Beige							
PBPA19007GY2	ASA 61 Gray							
PBPA19007UNF	Unfinished							
PBPA19008BK2	Black		13K		74K	8.75	5	4
PBPA19008CG2	Gray/Beige							
PBPA19008GY2	ASA 61 Gray							
PBPA19008UNF	Unfinished							
PBPA19010BK2	Black		13K		88K	10.50	6	8
PBPA19010CG2	Gray/Beige							
PBPA19010GY2	ASA 61 Gray							
PBPA19010UNF	Unfinished							
PBPA19012BK2	Black		13K		88K	12.25	7	8
PBPA19012CG2	Gray/Beige							
PBPA19012GY2	ASA 61 Gray							
PBPA19012UNF	Unfinished							
PBPA19014BK2	Black		13K		88K	14.00	8	8
PBPA19014CG2	Gray/Beige							
PBPA19014GY2	ASA 61 Gray							
PBPA19014UNF	Unfinished							
PBPA19015BK2	Black		13K		88K	15.75	9	8
PBPA19015CG2	Gray/Beige							
PBPA19015GY2	ASA 61 Gray							
PBPA19015UNF	Unfinished							
PBPA19017BK2	Black		13K		88K	17.50	10	8
PBPA19017CG2	Gray/Beige							
PBPA19017GY2	ASA 61 Gray							
PBPA19017UNF	Unfinished							

PBPA19019BK2 PBPA19019CG2 PBPA19019GY2 PBPA19019UNF	Black Gray/Beige ASA 61 Gray Unfinished		13K		88K	19.25	11	8
PBPA19021BK2 PBPA19021CG2 PBPA19021GY2 PBPA19021UNF	Black Gray/Beige ASA 61 Gray Unfinished		13K		88K	21.00	12	8
PBPA19022BK2 PBPA19022CG2 PBPA19022GY2 PBPA19022UNF	Black Gray/Beige ASA 61 Gray Unfinished		13K		88K	22.75	13	8
PBPA19024BK2 PBPA19024CG2 PBPA19024GY2 PBPA19024UNF	Black Gray/Beige ASA 61 Gray Unfinished		14K		95K	24.50	14	10
PBPA19026BK2 PBPA19026CG2 PBPA19026GY2 PBPA19026UNF	Black Gray/Beige ASA 61 Gray Unfinished		14K		95K	26.25	15	10
PBPA19028BK2 PBPA19028CG2 PBPA19028GY2 PBPA19028UNF	Black Gray/Beige ASA 61 Gray Unfinished		14K		102K	28.00	16	12
PBPA19029BK2 PBPA19029CG2 PBPA19029GY2 PBPA19029UNF	Black Gray/Beige ASA 61 Gray Unfinished		14K		102K	29.75	17	12
PBPA19031BK2 PBPA19031CG2 PBPA19031GY2 PBPA19031UNF	Black Gray/Beige ASA 61 Gray Unfinished		14K		102K	31.50	18	12

Unfinished Feature:



(click to enlarge)

Unfinished version is white paper covered on one side to protect finish - also used as a surface for a machining template

DOWNLOAD



[Rack panel catalog pages \(2\)](#) - Adobe Reader .pdf format (105K)

DOWNLOAD



[all accessories - catalog pages \(44\)](#) - Adobe Reader .pdf format (1,495K)

Mail Link To Our Catalog Department

[Provide full mailing address here for your FREE CATALOG via snail mail...](#)

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check