

Farnell In One Kit to Lapp Part Numbers Cross References

FIO Order Code	FIO Manufacturers order code	Description	LAPP Part No.
8602352	HBE6-FK-TE-PM-M20	Top Entry Hood M20 complete with panel base. Single lever on base complete with inserts and gland	19011000 10.0030 10.1900 10.1910 71201200
8602360	HBE6-FK-SE-PM-M20	Side Entry Hood M20 complete with panel base. Single lever on base complete with inserts and gland	19012000 10.0030 10.1900 10.1910 71200200
8602379	HBE10-FK-TE-PM-M20	Top Entry Hood M20 complete with panel base. Double levers on base complete with inserts and gland	19040100 10.0320 10.1920 10.1930 71201300
8602387	HBE10-FK-SE-PM-M20	Side Entry Hood M20 complete with panel base. Double levers on base complete with inserts and gland	19042100 10.0320 10.1920 10.1930 71200300
8602395	HBE16-FK-TE-PM-M20	Top Entry Hood M25 complete with panel base. Double levers on base complete with inserts and gland	19080000 10.0720 10.1940 10.1950 71201300
8602409	HBE16-FK-SE-PM-M20	Side Entry Hood M25 complete with panel base. Double levers on base complete with inserts and gland	19082000 10.0720 10.1940 10.1950 71200300
8602417	HBE24-FK-TE-PM-M20	Top Entry Hood M25 complete with panel base. Double levers on base complete with inserts and gland	19121000 10.1020 10.1960 10.1970 71201300
8602425	HBE24-FK-SE-PM-M20	Side Entry Hood M25 complete with panel base. Double levers on base complete with inserts and gland	19113000 10.1020 10.1960 10.1970 71200300
8602433	HA3-FK-TE-PM-M-M20	Top Entry Hood with M20 gland + panel mount base + male and female screw terminal 3 way inserts	19426500 10.4225 10.4200 10.4210
8602441	HA3-FK-TE-SE-M-M20	Top Entry Hood with M20 gland + side entry base + male and female screw terminal 3 way inserts	19426500 10.4235 10.4200 10.4210
8602450	HA4-FK-TE-PM-M-M20	Top Entry Hood with M20 gland + panel mount base + male and female screw terminal 4 way inserts	19426500 10.4225 10.4310 10.4320

8602468	HA4-FK-TE-SE-M-M20	Top Entry Hood with M20 gland + side entry base + male and female screw terminal 4 way inserts	19426500 10.4235 10.4310 10.4320
8602476	HA3-FK-TE-SM-M-M20	Top Entry Hood with M20 gland + surface mount base + male and female screw terminal 3 way inserts	19426500 19424500 10.4200 10.4210
8602484	HA4-FK-TE-SM-M-M20	Top Entry Hood with M20 gland + surface mount base + male and female screw terminal 4 way inserts	19426500 19424500 10.4310 10.4320
8602492	HA3-FK-TE-CH-M-M20	Top Entry Hood with M20 gland + coupler hood + male and female screw terminal 3 way inserts	19426500 19429500 10.4200 10.4210
8602506	HA4-FK-TE-CH-M-M20	Top Entry Hood with M20 gland + coupler hood + male and female screw terminal 4 way inserts	19426500 19429500 10.4310 10.4320
8602514	HA3-FK-TE-PM-P-M20	Top Entry Hood with M20 gland + panel mount base + male and female screw terminal 3 way inserts	19426000 10.4220 10.4200 10.4210 53111420
8602522	HA3-FK-TE-SE-P-M20	Top Entry Hood with M20 gland + side entry base + male and female screw terminal 3 way inserts	19426000 10.4230 10.4200 10.4210 53111420
8602530	HA4-FK-TE-PM-P-M20	Top Entry Hood with M20 gland + panel mount base + male and female screw terminal 4 way inserts	19426000 10.4220 10.4310 10.4320 53111420
8602549	HA4-FK-TE-SE-P-M20	Top Entry Hood with M20 gland + side entry base + male and female screw terminal 4 way inserts	19426000 10.4230 10.4310 10.4320 53111420
8602557	HA3-FK-TE-SM-P-M20	Top Entry Hood with M20 gland + surface mount base + male and female screw terminal 3 way inserts	19426000 19421900 10.4200 10.4210 53111420
8602565	HA4-FK-TE-SM-P-M20	Top Entry Hood with M20 gland + surface mount base + male and female screw terminal 4 way inserts	19426000 19421900 10.4310 10.4320 53111420
8602573	HA3-FK-TE-CH-P-M20	Top Entry Hood with M20 gland + coupler hood + male and female screw terminal 3 way inserts	19426000 19429000 10.4200 10.4210 53111420 × 2

8602581	HA4-FK-TE-CH-P-M20	Top Entry Hood with M20 gland + coupler hood + male and female screw terminal 4 way inserts	19426000 19429000 10.4310 10.4320 53111420 × 2
8602999	H-Q-5-KIT	Complete kit with hood, cable gland, inserts and pins	10431500 10432500 11.1953 11.1903 19426000 10.4220 53111520
8603006	KIT HV-HC	High current high voltage kit 40A/1000V	79020200 10.0030 10178999 10178998 71201300 Allen Key