MIXPAD[®] MXP124FX / MXP144FX

Analog Stereo Mixers with Effects and USB



The all-new MixPad® Series Analog Stereo Mixers with Effects and USB integrate Samson's commitment to quality, affordability and professional specs into two models: the compact 12-input MXP124FX and the full-featured 14-input MXP144FX. These lightweight mixers offer all of the sonic clarity, ease of use and premium performance that serious musicians demand.

The MixPad® FX mixers feature premium circuitry specifically designed to work with Samson's MDR (Maximum Dynamic Range) mic preamps to provide wide frequency range, definitive channel separation and natural response. This ensures that all of your mixes originate from pure, authentic audio signals, making the MixPad® FX mixers perfect for education, broadcast, band rehearsals and other live sound applications.

With 100 24-bit, low-noise digital effects, each MixPad® FX mixer offers a studio-inspired effects processor to give your mixes a professional touch. Both models also feature a high-integrity, bidirectional USB connection for recording a mix to your favorite DAW or integrating digital music files from your computer into a project.

The MXP124FX offers four MDR mic preamp channels, each with a 3-band EQ, Gain trim, high pass filter and pre-fader Aux send. It also has high-quality faders, not typical of such a small format mixer. Two of its mic channels feature single-knob compressors for studio-quality dynamic control without the non-stop tweaking of external gear. In addition, the MXP124FX features four Stacked-Stereo channels for increased input versatility and portability. Exceptional output flexibility makes the MXP124FX a worthy companion regardless of venue size, giving you precise fader control over your Main Mix, as well a Mix 2 output, headphone (Phones) monitoring with level control and a RCA Tape out for recording your performance.

The MXP144FX offers six MDR mic preamps with four of the channels equipped with single-knob compressors. All channels on the MXP144FX are controlled via precision 60mm faders and feature a 3-band EQ, Gain trim, high pass filter and pre-fader Aux send for your monitor mix. In addition, each channel on the MXP144FX has a mute switch and a post-fader Aux send for introducing external effects. The MXP144FX expands on the output options of the MXP124FX with XLR and 1/4" outs on the Main Mix.

Both MixPad[®] FX mixers have selectable 48-volt phantom power so you're free to mix in the warm, natural response of your favorite condenser microphones. Further catered to live performance, the MixPad[®] FX mixers include brightly colored knobs, as well as 4 (MXP124FX) or 8- (MXP144FX) segment LED level metering for safe and efficient operation in dark environments.

Portable, easy to use and jam-packed with features that ensure optimal control over your performance, Samson's MixPad® MXP124FX and MXP144FX represent a new era of possibility for affordable live mixers.

FEATURES

MXP124FX

- Ultra-low noise, high headroom analog mixer
 Four Class A, MDR (Maximum Dynamic Range) mic preamps with 3-band EQ
- Four Stacked-Stereo channels
- High-quality, precision faders
- Two single-knob, studio-quality compressors
- High-integrity, bidirectional USB interface
- 100 24-bit, low-noise digital effects
- One pre-fader Aux Send per channel for monitor mix
- All mic channels equipped with input Gain and
- high pass filters
- 48V Phantom Power for condenser microphones
- Multiple outputs: Main Mix, Mix 2, Phones and Tape
 USB/Tape inputs assignable to Main Mix or Mix 2/
- Osb/rape inputs assignable to main with or with 27 Phones outputs
 Optional min stand mount quailable
- Optional mic stand mount available

MXP144FX

- Ultra-low noise, high headroom analog mixer
- Six Class A, MDR (Maximum Dynamic Range) mic preamps
- Four stereo channels with multiple input options (1/4" and RCA)
- High-integrity, bidirectional USB interface
- 100 24-bit, low-noise digital effects
- Four TRS inserts for external signal processing
- 3-band active EQ
- High-quality, precision 60mm faders
- Four single-knob, studio-quality compressors
- Pre-fader Aux Send for monitor mix
- Post-fader Aux Send for external effects
- All mic channels equipped with input Gain and high pass filters
- 48V Phantom Power for condenser microphones
- Multiple outputs: Main Mix, Mix 2, Phones and Tape
- XLR and 1/4" Main Mix outputs
- USB/Tape inputs assignable to Main Mix or Mix 2/Phones outputs



MXP124FX



MXP144FX

MXP124FX

UPC	
SKU	SAMXP124FX
HEIGHT	
WIDTH	13"
DEPTH	5.75"
WEIGHT	7.5lb

MXP144FX

* DIMENSIONS AND WEIGHTS BOXED

** MASTER CARTON QUANTITY (ALL): 4

