

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0672983091](#)
Status: **Active**
Overview: [Consumer USB Products](#)
Description: Universal Serial Bus (USB) Shielded I/O Receptacle, Right Angle, Dual Stacked, Type A, 0.76µm Gold (Au) Plating, Black Housing, with 4 Beveled Metal Pins, Lead-Free

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-67298-001-001 \(PDF\)](#)
[Product Specification TS-67298-008-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family I/O Connectors
Series [67298](#)
Application Wire-to-Board
Comments 4 Beveled Metal Pins
Component Type Receptacle
Overview [Consumer USB Products](#)
Product Name USB 2.0
Type A
UPC 822350050913

Physical
Boot Color N/A
Circuits (Loaded) 8
Circuits (maximum) 8
Gender Receptacle
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 4.780/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.80mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Panel Mount Yes
Pitch - Mating Interface 2.00mm, 2.50mm
Pitch - Termination Interface 2.00mm, 2.50mm
Plating min - Mating 0.762µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 2
Surface Mount Compatible (SMC) No
Temperature Range - Operating 0°C to +50°C
Termination Interface: Style Through Hole
Waterproof / Dustproof No

Electrical
Current - Maximum per Contact 1.5A
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 30V DC



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per -ED/01/2017 (12 January 2017) Halogen-Free Status Not Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS Green Image ELV Not Relevant RoHS Phthalates Not Contained
---	--

Search Parts in this Series
[67298](#) Series

Mates With
USB Type A Plug

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-67298-001-001, TS-67298-008-001
SD-67298-008

This document was generated on 03/30/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION