

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0673298000**  
**Status:** **Active**  
**Overview:** Consumer USB Products  
**Description:** Universal Serial Bus (USB) Shielded I/O Receptacle, Type A, Single Upright Right Angle, Solder Tail Length 2.00mm, Kinked Pins, PCB Thickness 1.20mm and 1.60mm, Gold (Au) Flash, Lead-Free

**Documents:**

[3D Model](#) [Packaging Specification PK-67329-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-89485 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**


Product Family I/O Connectors  
Series [67329](#)  
Application Wire-to-Board  
Comments Standard Mount Type  
Component Type Receptacle  
Overview [Consumer USB Products](#)  
Product Name USB 2.0  
Type A  
UPC 822350416887

**Physical**

Boot Color N/A  
Circuits (Loaded) 4  
Circuits (maximum) 4  
Flammability 94V-0  
Gender Receptacle  
Lock to Mating Part Yes  
Material - Plating Mating Gold  
Material - Plating Termination Tin  
Net Weight 2.025/g  
Number of Rows 4  
Orientation Upright  
PC Tail Length 2.00mm  
PCB Locator Yes  
PCB Retention Yes  
PCB Thickness - Recommended 1.60mm  
Packaging Type Tray  
Panel Mount No  
Pitch - Mating Interface N/A  
Pitch - Termination Interface 1.40mm  
Plating min - Mating 0.102µm  
Plating min - Termination 2.540µm  
Polarized to Mating Part Yes  
Polarized to PCB Yes  
Ports 1  
Surface Mount Compatible (SMC) Yes  
Termination Interface: Style Through Hole  
Waterproof / Dustproof No

**Electrical**

Current - Maximum per Contact 1.0A



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[67329](#) Series

**Mates With**

USB Type A Plug

Shield Type  
Shielded

Full Shield  
Yes

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification

PK-67329-001

Product Specification

PS-89485

Sales Drawing

SD-67329-801

This document was generated on 03/27/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**