

Part Number: [0643221029](#)
Status: Active
Overview: [CMC and CMX Sealed, Hybrid, Modular Connectors](#)
Description: 0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.75mm²


Documents:

3Dモデル	圧着仕様書 AS-64322-001-CH-001 (PDF)
図面 (PDF)	圧着仕様書 AS-64322-001-FR-001 (PDF)
製品仕様書 PS-64319-002-001 (PDF)	圧着仕様書 AS-98420-001-001 (PDF)
製品仕様書 PS-64326-001-001 (PDF)	圧着仕様書 AS-98420-001-CH-001 (PDF)
圧着仕様書 AS-64318-002-001 (PDF)	圧着仕様書 AS-98420-001-FR-001 (PDF)
圧着仕様書 AS-64318-002-CH-001 (PDF)	圧着仕様書 AS-98420-001-SP-001 (PDF)
圧着仕様書 AS-64318-002-FR-001 (PDF)	圧着仕様書 AS-98420-002-001 (PDF)
圧着仕様書 AS-64318-002-SP-001 (PDF)	圧着仕様書 AS-98420-002-CH-001 (PDF)
圧着仕様書 AS-64319-002-001 (PDF)	圧着仕様書 AS-98420-002-FR-001 (PDF)
圧着仕様書 AS-64319-002-CH-001 (PDF)	圧着仕様書 AS-98420-002-SP-001 (PDF)
圧着仕様書 AS-64319-002-FR-001 (PDF)	梱包仕様書 PK-98913-001-001 (PDF)
圧着仕様書 AS-64319-002-SP-001 (PDF)	RoHS Certificate of Compliance (PDF)
圧着仕様書 AS-64322-001-001 (PDF)	

一般用途コメント	Signal, 電線対基板 * Current tested on a 5 terminals loaded connector, current for temperature increase of 40° C. Current max = 6A for 0.635mm Terminal (0.75mm ² wire)
Crimp Quality Equipment	有
概要	CMC and CMX Sealed, Hybrid, Modular Connectors
製品名	CMC, CPターミナル
UPC	883906129477
機械的性能/材質	
ジェンダー	フィメール
材質 - 金属部	りん青銅
材質 - 嵌合部メッキ	錫
材質 - ターミナルメッキ	錫
Net Weight	0.160/g
梱包形態	リール
嵌合部メッキ厚	1.524µm, 3.048µm
実装スタイル	圧着またはコンプレッション
被覆外径	1.65-1.80mm
電線サイズ (AWG)	18
Wire Size mm ²	0.75
電気的性能	
最大定格電流	6.0A
最大定格電圧	14V DC
Solder Process Data	
Lead-freeProcess Capability	N/A

参考情報

図面・仕様書情報
 圧着仕様書
 AS-64318-002-001, AS-64318-002-CH-001, AS-64318-002-FR-001, AS-64318-002-SP-001, AS-64319-002-001, AS-64319-002-CH-001,



EU ELV
Compliant

EU RoHS
Compliant

China RoHS
Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[64322 Series](#)

Mates With
 CMC Connector [64318](#), [64319](#), [64320](#), [64321](#), [64326](#)

Use With
 CMC Connector [64318](#), [64319](#), [64320](#), [64321](#), [64326](#)

梱包仕様書
製品仕様書
製品図面

AS-64319-002-FR-001, AS-64319-002-SP-001,
AS-64322-001-001, AS-64322-001-CH-001,
AS-64322-001-FR-001, AS-98420-001-001,
AS-98420-001-CH-001, AS-98420-001-FR-001,
AS-98420-001-SP-001, AS-98420-002-001,
AS-98420-002-CH-001, AS-98420-002-FR-001,
AS-98420-002-SP-001
PK-98913-001-001
PS-64319-002-001, PS-64326-001-001
SD-64322-001-000

This document was generated on 09/12/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION