

TLIGHT-WWCW

COLD/WARM WHITE LED FRESNEL PROJECTOR


FOR STAGE & THEATRE 200W



FEATURES

- 4 DMX channels
- DMX, manual control with master/slave and dimmer
- Strobe functions
- Black aluminium housing

Power supply.....	100-250V~ 50/60Hz
Consumption.....	200W
Colour temperature.....	3200K±150. 5600K±150
.....	Warm white/Cold white
LED lifespan.....	Approx. 30.000 hours
CRI.....	Ra≥92
BEAM opening.....	15-50°
Dimensions.....	450 x 259 x 240mm
Weight.....	6.5kg



CODE: **16-2802**

CODE EAN: **5420047141194**



LOGISTIC VALUES

Height / Hauteur.....	47,5cm
Width / Largeur.....	34,5cm
Depth / Profondeur.....	31,5cm
Volume.....	0,052m ³
Net weight / Poids net.....	6,5kg
Gross weight / Poids brut.....	7,5kg
Carton qty / Colisage.....	2 pcs.

TLIGHT-WWCW

PROJECTEUR FRESNEL

POUR THEATRE ET SCENE


A LED BLANC CHAUD/BLANC FROID 200W



FEATURES

- 4 canaux DMX
- Contrôle DMX, manuel avec mode maître-esclave et dimmer
- Fonctions Stroboscope
- Boîtier en aluminium noir

Alimentation	100-250V~ 50/60Hz
Consommation	200W
Température de couleur	3200K±150. 5600K±150
.....	Blanc chaud/Blanc froid
Durée de vie des led	Approx. 30.000 hours
CRI	Ra≥92
Ouverture BEAM	15-50°
Dimensions	450 x 259 x 240mm
Poids	6.5kg



CODE: **16-2802**

CODE EAN: **5420047141194**



LOGISTIC VALUES

Height / Hauteur	47,5cm
Width / Largeur	34,5cm
Depth / Profondeur	31,5cm
Volume	0,052m ³
Net weight / Poids net	6,5kg
Gross weight / Poids brut	7,5kg
Carton qty / Colisage	2 pcs.

TLIGHT-WWCW


PROYECTOR FRESNEL DE LED BLANCO CALIDO / BLANCO FRIO 200W PARA TEATRO Y ESCENARIOS



FEATURES

- 4 canales DMX
- Control DMX, manual con modo maestro-esclavo y dimmer
- Función Estroboscopio
- Carcasa en Aluminio negro

Alimentación.....	100-250V~ 50/60Hz
Consumo.....	200W
Temperatura de color.....	3200K±150. 5600K±150
.....	Blanco cálido /Blanco frio
Duración de la vida de los LEDS.....	Approx. 30.000 hours
CRI.....	Ra≥92
Apertura BEAM.....	15-50°
Dimensiones.....	450 x 259 x 240mm
Peso.....	6.5kg



CODE: **16-2802**

CODE EAN: **5420047141194**



LOGISTIC VALUES

Height / Hauteur.....	47,5cm
Width / Largeur.....	34,5cm
Depth / Profondeur.....	31,5cm
Volume.....	0,052m ³
Net weight / Poids net.....	6,5kg
Gross weight / Poids brut.....	7,5kg
Carton qty / Colisage.....	2 pcs.