

# RGBW LED FRESNEL PROJECTOR FOR STAGE & THEATRE 200W




## TLIGHT-RGBW

### FEATURES

- 9 DMX channels
- DMX, manual control with master/slave and RGBW dimmer
- 11 programmes with DMX controlled speed adjustment
- Black aluminium housing

Power supply.....	100-250V~ 50/60Hz
Consumption.....	200W
Colour temperature.....	3200K±150. 5600K±150
.....	.....RGBW
LED lifespan.....	Approx. 30.000 hours
CRI.....	Ra≥92
BEAM opening.....	15-50°
Dimensions.....	450 x 259 x 240mm
Weight.....	6.5kg



CODE: **16-2803**  
 CODE EAN: **5420047141200**



### LOGISTIC VALUES

Height / Hauteur.....	47,5cm
Width / Largeur.....	34,5cm
Depth / Profondeur.....	31,5cm
Volume.....	0,052m <sup>3</sup>
Net weight / Poids net.....	6,5kg
Gross weight / Poids brut.....	7,5kg
Carton qty / Colisage.....	2 pcs.

# PROJECTEUR FRESNEL POUR THEATRE ET SCENE A LED RGBW 200W




## TLIGHT-RGBW

### FEATURES

- 9 canaux DMX
- Contrôle DMX, manuel avec mode maître-esclave et dimmer RGBW
- 11 programmes avec réglage de vitesse par DMX
- Boîtier en aluminium noir

Alimentation .....	100-250V~ 50/60Hz
Consommation .....	200W
Température de couleur .....	3200K±150. 5600K±150
.....	.....RGBW
Durée de vie des led.....	Approx. 30.000 hours
CRI.....	Ra≥92
Ouverture BEAM.....	15-50°
Dimensions.....	450 x 259 x 240mm
Poids .....	6.5kg



CODE: **16-2803**

CODE EAN: **5420047141200**



### LOGISTIC VALUES

Height / Hauteur .....	47,5cm
Width / Largeur .....	34,5cm
Depth / Profondeur .....	31,5cm
Volume .....	0,052m <sup>3</sup>
Net weight / Poids net.....	6,5kg
Gross weight / Poids brut .....	7,5kg
Carton qty / Colisage .....	2 pcs.

# PROYECTOR FRESNEL DE LED RGBW 200W PARA TEATRO Y ESCENARIOS



## TLIGHT-RGBW

### FEATURES

- 9 canales DMX
- Control DMX, manual con modo maestro-esclavo y dimmer RGBW
- 11 programas con ajuste de velocidad por DMX
- Carcasa en Aluminio negro

Alimentación.....	100-250V~ 50/60Hz
Consumo.....	200W
Temperatura de color.....	3200K±150. 5600K±150
.....	.....RGBW
Duración d ela vida d ellos LEDS.....	Approx. 30.000 hours
CRI.....	Ra≥92
Apertura BEAM.....	15-50°
Dimensiones.....	450 x 259 x 240mm
Peso.....	6.5kg



CODE: **16-2803**

CODE EAN: **5420047141200**



### LOGISTIC VALUES

Height / Hauteur.....	47,5cm
Width / Largeur.....	34,5cm
Depth / Profondeur.....	31,5cm
Volume.....	0,052m <sup>3</sup>
Net weight / Poids net.....	6,5kg
Gross weight / Poids brut.....	7,5kg
Carton qty / Colisage.....	2 pcs.