

ITEM	PART#	DESCRIPTION	QTY	UOM
A	510651000	Micro-Latch 2.0 Rec Housing 10P	1	PC
B	503728000	Micro-Latch 2.0 Crimp R Term Tin #22-26	10	PC
C	--	PAPER PRINTED PAPER WHITE (S100X150YAJ)	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A3	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A4	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A5	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A6	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A7	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A8	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A9	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A10	--	1X22AWG DISC SR-PVC BK UL10002	BLACK

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A




TABLE			
PART NUMBER	L1	L2 (REF)	TITLE
2196791100	50±3	15	Micro Latch 2.0 R-S 10ckt 50mm disc Sn
2196791101	100±3	15	Micro Latch 2.0 R-S 10ckt 100mm disc Sn
2196791102	150±4	15	Micro Latch 2.0 R-S 10ckt 150mm disc Sn
2196791103	300±4	15	Micro Latch 2.0 R-S 10ckt 300mm disc Sn
2196791104	600±6	15	Micro Latch 2.0 R-S 10ckt 600mm disc Sn

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/02/27	A	INITIAL RELEASE	SAIKIG

- NOTES
1. Connector view shown is from mating side.
 2. Label text must be 2mm max. in height with Arial font.
 3. Label must be wrapped in Flag type on a single cable.
 4. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning Dia must be 0.9 mm Max.

FUNCTIONAL SYMBOLS $\nabla_A = 0$ $\nabla_E = 0$ $\nabla_P = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		<p>SEE TABLE</p>
	DIMENSION UNITS	SCALE	EC NO: 697300		
	mm	NTS	DRWN: SAIKIG 2022/02/21		
	GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: MNARAYAN01 2022/03/08		
ANGULAR TOL ± °		APPR: MNARAYAN01 2022/03/08		PRODUCT CUSTOMER DRAWING	
4 PLACES ±		INITIAL REVISION:		DOCUMENT NUMBER	DOC TYPE
3 PLACES ±		DRWN: SAIKIG 2022/02/21		2196791100	PSD
2 PLACES ±		APPR: MNARAYAN01 2022/03/08		000	REVISION
1 PLACE ±		MATERIAL NUMBER		GENERAL MARKET	A
0 PLACES ±		THIRD ANGLE PROJECTION		CUSTOMER	SHEET NUMBER
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING		SEE TABLE	1 OF 1
		SERIES		GENERAL MARKET	
		A4-SIZE			
		219679			