

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

67298-3091

Status:

Active

Overview:

Consumer USB Products

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Right Angle, Dual Stacked, Type A, 0.76µm Gold (Au) Plating, Black Housing, with 4 Beveled Metal Pins, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-67298-001 (PDF)

Test Summary TS-67298-008 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	I/O Connectors
Series	67298
Application	Wire-to-Board
Comments	4 Beveled Metal Pins
Component Type	Receptacle
Overview	Consumer USB Products
Product Name	USB
Type	A
UPC	822350050913

Physical

Boot Color	N/A
Circuits (Loaded)	8
Circuits (maximum)	8
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	4.780/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0°C to +50°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No

Electrical

Current - Maximum per Contact	1.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V DC




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

67298Series

Mates With

USB Type A Plug

Material Info

Reference - Drawing Numbers

Product Specification	PS-67298-001
Sales Drawing	SD-67298-008
Test Summary	TS-67298-008

This document was generated on 10/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION