

USB-C to USB-A Adapter, Right-Angled, USB 5Gbps, 3A, USB-C Male to USB-A Female Converter, Durable Metal Housing - Thunderbolt Compatible

Product ID: USB31CAADGCPRA



Connect a USB-A device to a USB-C laptop or convert a USB-A cable to Type-C, using this compact USB-C to USB-A Male to Female adapter. The connector markings enable quick visual identification, distinguishing this adapter from other similar-looking or unmarked USB-C adapters. Eliminate guesswork and always choose the appropriate adapter that supports USB 5Gbps.

The USB-C to USB-A adapter is universally compatible with any Operating System. Simple plug-and-play setup enables instant deployment. The adapter supports USB 5Gbps and USB 2.0 (480Mbps), and facilitates up to 5V/3A output from a powered USB-C connection such as a wall charger. This enables up to 15W charging to a USB-A device from a USB-C source. Please note that USB-C video and Power Delivery are not supported.

The USB C to A adapter has a durable aluminum alloy housing that protects against wear and tear. The nickel-plated connectors are designed for long-lasting reliability and performance.

Certifications, Reports and Compatibility



Applications

- Right angled connector reduces cable strain in tight spaces
- Charge a USB-C device with up to 15W from a powered USB-A connection
- Slim, compact housing is durable and will not obstruct adjacent ports

Features

- **RIGHT ANGLED USB-C ADAPTER:** Compact Right Angled USB-C Male to USB-A Female adapter connects neatly to a USB-C host; Ideal for installations where space is limited; Clear connector markings with data/power specs enable easy identification at a glance
- **QUALITY CONSTRUCTION:** Aluminum alloy outer housing enhances durability and wear protection; Slim design prevents the obstruction of adjacent device ports; Durable Nickel-plated connectors ensure consistent data throughput
- **COMPATIBILITY:** Versatile compatibility with USB-A cables and devices; Supports USB-C laptops and portable devices; Charge a portable USB-C device from a USB-A charger (up to 15W); **NOTE:** Please confirm compatibility between the USB-A device and USB-C host
- **QUICK INSTALLATION:** Ideal for mounted devices with bottom or rear-facing ports; Right-angled connector reduces cable and port strain from bending; Plug-and-play design requires no drivers for a hassle-free setup; Compatible with any Operating System
- **RELIABLE TRANSMISSION:** USB-C to USB-A adapter supports 5Gbps data transfer; Backward compatibility with USB 480Mbps (USB 2.0) for legacy devices; Supports up to 5V/3A output from a USB-A charger; **NOTE:** USB-C video and Power Delivery are not supported

Hardware

| | |
|---------------------------|---------|
| Warranty | 2 Years |
| Active or Passive Adapter | Passive |
| Ports | 1 |
| Connector Plating | Nickel |

Performance

| | |
|----------------------------|-------|
| Maximum Data Transfer Rate | 5Gbps |
|----------------------------|-------|

Connector(s)

| | |
|-------------|---|
| Connector A | 1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps) |
| Connector B | 1 - USB Type-A (9 pin, 5 Gbps) |

Power

| | |
|---------------|-------|
| Input Voltage | 5V DC |
| Input Current | 3A |

Environmental

| | |
|-----------------------|-------------------------------|
| Operating Temperature | 0 to 40 (32°F to 104°F) |
|-----------------------|-------------------------------|

| | |
|---------------------|---------------------------------|
| Storage Temperature | -10 to 70 (14°F to 158°F) |
| Humidity | 10%~90% |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Connector Style | Right Angled |
| Material | Aluminum |
| Product Length | 1.0 in [2.6 cm] |
| Product Width | 0.6 in [1.4 cm] |
| Product Height | 0.5 in [1.2 cm] |
| Weight of Product | 0.2 oz [5.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 4.9 in [12.5 cm] |
| Package Width | 3.5 in [9.0 cm] |
| Package Height | 0.2 in [5.0 mm] |
| Shipping (Package) Weight | 0.2 oz [5.2 g] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - USB-C to Right Angle USB-A Adapter - M/F |
|---------------------|--|

**Product appearance and specifications are subject to change without notice.*