

# PRODUCT DATASHEET

## NIGHTLUX Stair Silver

**NIGHTLUX Stair | Nightlights for stairs illumination, battery-powered**



---

### AREAS OF APPLICATION

- For a very large range of uses
- Indoor and outdoor
- Stairways
- Along corridors for way-finding
- Entrances / Hallways

---

### PRODUCT BENEFITS

- Attractive and functional design
- Economical operation due to low power consumption
- Easy and fast mounting on nearly every surface (adhesive tape or screws)
- Accessories for flexible mounting options included

---

### PRODUCT FEATURES

- Integrated light and motion sensor
- Available in two housing colors
- Switch for Auto- or On/Off-Mode
- Type of protection: IP54
- Downward light emission for floor illumination



**TECHNICAL DATA**

Electrical data

Nominal wattage	0.25 W
Operating mode	Battery
Nominal voltage	4.5 V
Mains frequency	0 Hz


Photometrical data

Color temperature	4000 K
Color rendering index Ra	>80
Light color (designation)	Cool White
Luminous flux	10 lm
Luminous efficacy	40 lm/W

Luminaire sensor data

Type of sensor	Light / Motion
Sensor technology	Passive infrared (PIR)

Dimensions & weight



Length	28.0 mm
Width	84.0 mm
Height	73.0 mm
Product weight	95.00 g

Colors & materials

Body material	Acrylonitrile butadiene styrene (ABS)
Product color	Silver
Housing color	Silver

## Temperatures &amp; operating conditions

Ambient temperature range	0...+25 °C
---------------------------	------------

## Lifespan

Number of switching cycles	10000
Lifespan	25000 h

## Additional product data

Mounting type	Surface
Mounting location	Wall

## Capabilities

Dimmable	No
LED module replaceable	Not replaceable

## Certificates &amp; standards

Protection class	III
Type of protection	IP54
Standards	CE/RoHS/REACH

## EQUIPMENT / ACCESSORIES

- Batteries included: 3x1.5 V LR03 (AAA)

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075260757	Blister 1	31 mm x 140 mm x 195 mm	115.00 g	0.83 dm <sup>3</sup>
4058075260764	Shipping carton box 6	198 mm x 154 mm x 210 mm	799.00 g	6.40 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.