


Tapo Smart IoT Hub with Chime



Tapo H100



Smart Alarm



Smart Doorbell



19 Ringtone
Options



Up to 64
Devices



// Tapo Smart Ecosystem

Tapo is the easy way to turn your home into a smart home. At the center of it all is the Tapo Hub. With superior ultra-low-power performance, Tapo Hub connects wirelessly with a wide range of Tapo accessories. So you can easily control and monitor your home from anywhere.



// 3 in 1 Device for All Your Needs[†]



Tapo H100



Smart IoT Hub

Use a long-distance, low-power wireless protocol to connect to battery-powered Tapo devices.



Smart Alarm

Protect your home security by coordinating with Tapo smart sensors (motion sensor, window/door sensor, and more).



Smart Doorbell

Easily build your smart doorbell system, by installing the Tapo smart button on the door.

[†]To build a smart alarm or smart doorbell, the Tapo Hub will need to work with certain smart devices.

// Features

- **Ultra-Long Distance Connection** – With the low frequency wireless protocol, Tapo hub sends and receives data steadily throughout your home.
- **Ultra-Low-Power Performance** – Connect wirelessly with a wide range of Tapo accessories and never let your guard down.
- **Real-Time Notifications** – Monitor your entire home and all connected devices to get instant alerts when the activity is detected. The built-in alarm gives you more than enough protection.
- **19 Ringtone Options** – 90 DB[‡] built-in multiple ringtones for your customized scenarios.
- **Up to 64 Devices[#]** – Connect multiple devices to create a smart ecosystem for your home.
- **Device Sharing** – Easily share management permissions with each member of your family.
- **Easy Setup and Use** – No wiring required. Set up quickly and manage easily through the free Tapo app.
- **Flame-Retardant[△]** - PC flame-retardant materials help minimize burning hazards.

[‡]Decibel values may vary by ringtones and environmental factors.

[#]The max connections may vary by the types of smart devices connected.

[△]Made with V-0 (UL94) flame-retardant materials.

// Specifications


General

- Rating: AC, 100-240 V, 50/60 Hz
- Wireless: 2.4 GHz Wi-Fi, 868 MHz for connected devices[§]
- Material: V-0 (UL-94) Flame retardant PC[△]
- LED&Button: Status LED, SYNC/Silence Button
- Built-in: 90 DB[‡] alarm, 19 ringtones



Others

- Package Contents:
Smart Hub Tapo H100
Quick Start Guide
- Certifications: CE, UKCA, RoHS
- Operating Temperature: 0 °C– 40 °C (32°F–104°F)
- Operating Humidity: 10%–90%RH, Non-condensing
- Dimensions: 72×62.6×51 mm (2.8×2.5×2 inch)



[§]The specific working frequency is 863 MHz ~ 868.6 MHz.

[△]Made with V-0 (UL94) flame-retardant materials.

[‡]Decibel values may vary by ringtones and environmental factors.

Please do not use in damp environments or outdoors. For more information, please visit <https://www.tapo.com/>

Specifications are subject to change without notice. All brands and product names are trademarks or registered trademarks of their respective holders.

©2022 TP-Link