



LED MONITOR

Vero V7 series- V247Y E

- FHD resolution with ZeroFrame Design
- 85% PCR, 5% OBP 100% recyclable packaging
- TCO/ENERGY STAR/EPEAT Silver certified
- AMD FreeSync™ technology
- 100Hz refresh rate, flicker-free
- sRGB 99%
- IPS panel with 178° wide view angle
- Robust stand design with strong stability
- Acer VisionCare 2.0 for comfy viewing
- TUV/Eyesafe™ certified; protect eyes by reducing harmful blue light while maintaining high color accuracy



Specifications

Panel	Display Size	23.8"
	Maximum Resolution and Refresh Rate	VGA:1920x1080@75Hz HDMI:1920x1080@100Hz DP:1920x1080@100Hz
	Glare	No
	Panel	IPS
	Response Time	4ms (G to G)
	Contrast Ratio	100 million:1 max (ACM); 1300:1 (Typ.)
	Brightness	250 nits (cd/m ²)
	Viewing Angle	178° (H), 178° (V)
	Colors	16.7M
	Bits/Color Gamut	6Bit+FRC/ sRGB 99%
System	Input Signal	1VGA+1HDMI(1.4);
	VESA Wall Mounting	100 x 100 mm
	Speaker	N/A
	Power Supply (100 - 240 V)	Internal
	Tilt	-5°~ 25°

Feature Highlights

Professional Performance

- 23.8" Full HD resolution
- ZeroFrame form factor
- AMD FreeSync™
- 100Hz refresh rate, flicker-free
- Acer Display Widget
- sRGB 99%
- 6 axis color adjustment
- 178° wide view angle

Ergonomic design

- Robust stand design with strong stability
- VESA supportive

Comfort and protection

- BlueLight Shield™ Pro technology
- Acer Flicker-less technology
- Low dimming technology
- Acer ComfyView™ Display
- 85% PCR, 5% OBP, 100% recyclable packaging
- TCO, Energy Star and EPEAT Silver certification
- TUV/Eyesafe™ certified; protect eyes by reducing harmful blue light while maintaining high color accuracy



Full HD LED monitor



Clearer, sharper images in full high-definition color. Acer monitors brings users into a perfect colorful world in FHD 1920 x 1080, and provides the finest natural and sharp original quality 100,000,000:1 contrast ratio.



Eco-Display

As part of our commitment to sustainable operations and corporate social responsibility, Acer uses methods to carry out product design and material management distinctly meant to reduce environmental impact.



In-Plane Switching technology

The zero-frame design maximizes its viewing area and provides a more seamless viewing experience for multi-monitor setups.



Acer VisionCare 2.0

Acer VisionCare technology incorporates several features that take into consideration prolonged usage by heavy users such as programmers, writers, and graphic designers to reduce eye strain and provides a more comfortable viewing experience.

About Acer

Established in 1976, Acer is an information and communication technology company dedicated to the research, design, marketing, sale and support of innovative products that enhance people's lives. Acer's green supply chain delivers environmentally friendly PCs, displays, projectors, servers, tablets and smartphones — tools our customers need to explore beyond limits and experience more. Ranked No. 3 for notebooks globally (IDC 2012), Acer employs 8,000 people, and 2011 revenues reached US\$15.7 billion. Please visit www.acer.com for more information.

