

Standard Nylon Cable Ties

Natural and Black

multicomp PRO


**RoHS
Compliant**



Description

Durable one-piece nylon (polyamide) design for reliable performance. Outside serrations minimize damage to cables, while still providing high tensile strength.

Diagram



Specifications

Cable Tie Material : Nylon (Polyamide)
 Colour : Natural and Black
 Tip Style : Curved

Part Number Table

Description	Length		Width		Max. Bundle Dia		Min. Tensile Strength	Part Number			
	mm	Inch	mm	Inch	mm	Inch		Natural		Black	
Standard Nylon Cable Ties	80	3.125	2.4	0.093	16	0.625	18 (8)	SPC35190	SPC35211	SPC35224	SPC35245
	100	4	2.5		22	0.859		SPC35191	SPC35212	SPC35225	SPC35246
	142	5.5			35	1.375		-	SPC35213	SPC35226	SPC35247
	165	6.5			43	1.687		SPC35193	SPC35214	SPC35227	SPC35248
	203	8			55	2.156		SPC35194	SPC35215	SPC35228	SPC35249
	142	5.5			3.2	34		1.344	SPC35195	SPC35216	SPC35229
	203	8	0.141	53		2.093	SPC35196	SPC35217	SPC35230	SPC35251	
	250	10		68		2.672	SPC35197	SPC35218	SPC35231	SPC35252	
	292	11.5		82		3.25	SPC35198	SPC35219	SPC35232	SPC35253	
	300	11.8	4.8	0.187	83	3.27	40 (18)	SPC35203	N/A	SPC35237	N/A
	368	14.5	3.6	0.141	105	4.125		SPC35199	N/A	SPC35233	N/A
	160	6.25	4.8	0.187	39	1.531	50 (22)	SPC35200	SPC35220	SPC35234	SPC35254
	190	7.5			49	1.922		SPC35201	SPC35221	SPC35235	SPC35255
	203	8			52	2.203		SPC35202	SPC35222	SPC35236	SPC35256
	368	14.5			105	4.125		SPC35204	N/A	SPC35238	N/A
	450	17.75			131	5.156		SPC35205		SPC35239	
	550	21.687			162	6.375		SPC35206		SPC35240	
	203	8	7.6	0.297	52	2.045	120 (55)	SPC35207	SPC35223	SPC35241	SPC35257
	300	11.875			80	3.141		SPC35208	N/A	SPC35242	N/A
	380	15			105	4.125		SPC35209		SPC35243	
	450	17.75			128	5.032		175 (80)		SPC35210	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO