

Insulation Resistance Tester **multicomp** PRO



Specifications

Basic Functions	Range	Best Accuracy
Insulation Resistance	0.5MΩ to 100GΩ	±(3% +5)
Testing Voltage	500V / 1,000V / 1,500V / 2,500V	0 to +20%
DC Voltage	600V	±(2% +5)
AC Voltage		

Special Functions

Auto Ranging	-	-
Short Circuit Current	-	<1.8mA
Data Logging	-	18
Data Recall	-	-
Sleep Mode	-	-
Polarization Index (PI)	-	-
Timer	Around 15 mins	-
Compare	-	-
Battery Display	-	-
White Display Backlight	-	-
Over Range and High Voltage Warning	-	-
USB	-	-
Maximum Display	9999	-
Analogue Bar Graph	-	-

General Characteristics

Power	1.5V Alkaline Battery (LR14) × 8
LCD Size	123mm × 58mm
Product Colour	Orange and Grey
Product Net Weight	1.8kg
Product Size	202mm × 155mm × 94mm

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO

Insulation Resistance Tester **multicomp** PRO

Accessories	Qty.	Note
Operating Manual	1 piece	-
Adapter	2 pieces	1. UK three-pin square plug AC230V 50/60Hz 65mA DC14.5V 600mA 2. European style two-pin round plug AC230V 50/60Hz 65mA DC14.5V 600mA
Double plug alligator clip test leads-red	1 piece	RG58C doubl insulation conductor, length 1200mm ±20mm
Alligator clip test leads-green	1 piece	Ø4.5mm wrapped double insulated wire, [72×0.12TC×1C+S(50×0.12)], length:1200±20mm
Alligator clip test leads-black	1 piece	Ø4.5mm double insulated wire, (37×0.08BC×7 strands), length: 1200±20mm
Battery	8 pieces	1.5V R14 ×8, replaceable
USB interface cable	1 piece	USB/AM+USB/BM, length: 1m UL2725 28AWG+26AWG
Software	1 piece	-
ABS Tool case	1 piece	-

Part Number Table

Description	Part Number
Tester, Insulation, Resistance	72-9405

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO