

USB-C to USB-A Adapter, USB 5Gbps, 3A, USB-C Male to USB-A Female Converter, Durable Metal Housing - Thunderbolt Compatible

Product ID: USB31CAADGCP



Connect a USB-A device to a USB-C laptop or convert a USB-A cable to Type-C, using this compact USB-C to USB-A Male to Female adapter. The connector markings enable quick visual identification, distinguishing this adapter from other similar-looking or unmarked USB-C adapters. Eliminate guesswork and always choose the appropriate adapter that supports USB 5Gbps.

The USB-C to USB-A adapter is universally compatible with any Operating System. Simple plug-and-play setup enables instant deployment. The adapter supports USB 5Gbps and USB 2.0 (480Mbps), and facilitates up to 5V/3A output from a powered USB-C connection such as a wall charger. This enables up to 15W charging to a USB-A device from a USB-C source. Please note that USB-C video and Power Delivery are not supported.

The USB C to A adapter has a durable aluminum alloy housing that protects against wear and tear. The nickel-plated connectors are designed for daily use, and features gold-tipped contacts to minimize signal loss for long-lasting reliability and performance.

Certifications, Reports and Compatibility



Applications

- Connect a USB-A device to a USB-C laptop or host
- Charge a USB-A device with up to 15W from a USB-C charger or port
- Slim, compact housing is durable and will not obstruct adjacent ports

Features

- **USB-C to USB-A ADAPTER:** Use this slim and compact USB Type-C Male to Type-A Female adapter to convert and connect a USB-A peripheral device to a USB-C host; Connector markings with data/power specs for easy identification at-a-glance
- **QUALITY CONSTRUCTION:** Aluminum alloy outer housing enhances durability and wear protection; Slim design prevents the obstruction of adjacent device ports; Nickel-plated connectors with gold-tipped contacts ensure consistent data throughput
- **RELIABLE TRANSMISSION:** USB-C to USB-A adapter supports 5Gbps data transfer; Backward compatibility with USB 480Mbps (USB 2.0) for legacy devices; Supports up to 5V/3A output from a USB-C charger; NOTE: USB-C video and Power Delivery are not supported
- **COMPATIBILITY:** Versatile compatibility with USB-A cables and devices; Supports USB-C laptops and portable devices; Charge a portable USB-A device from a USB-C charger (up to 15W); NOTE: Please confirm compatibility between the USB-A device and USB-C host
- **QUICK INSTALLATION:** Simple plug-and-play design requires no driver for quick and hassle-free setup; Works on any Operating System; Install the adapter directly to a USB-A male connection and connect to a USB-C host or hub

Hardware

Warranty	2 Years
Active or Passive Adapter	Passive
Ports	1
Connector Plating	Nickel

Performance

Maximum Data Transfer Rate	5Gbps
----------------------------	-------

Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
Connector B	1 - USB Type-A (9 pin, 5 Gbps)

Power

Input Voltage	5V DC
Input Current	3A

Environmental

Operating Temperature	0 to 40 (32°F to 104°F)
-----------------------	-------------------------------

Storage Temperature	-10 to 70 (14°F to 158°F)
Humidity	10%~90%

Physical Characteristics

Color	Black
Connector Style	Straight
Product Length	1.1 in [2.7 cm]
Product Width	0.6 in [1.6 cm]
Product Height	0.3 in [8.2 mm]
Weight of Product	0.1 oz [4.0 g]

Packaging Information

Package Length	4.9 in [12.5 cm]
Package Width	3.5 in [9.0 cm]
Package Height	0.2 in [5.0 mm]
Shipping (Package) Weight	0.2 oz [6.0 g]

What's in the Box

Included in Package	1 - USB-C to USB-A Adapter - M/F
---------------------	----------------------------------

**Product appearance and specifications are subject to change without notice.*