



# TYPE - CLL



				Nominal	Dimensions			Std	Footage
Type	US Trade Size	MM	Nw	Inside	Outside	Min. Inside Bend Radius Static	Wt. (LBS.)/100Ft	Length	Part #
CLL-10	3/8"	16	12	.452"(11.5mm)	.622"(15.8mm)	0.7"	3.4	50	790818
CLL-11	1/2"	20	17	.633"(16.1mm)	.826"(21.0mm)	0.8"	4.4	50	791818
CLL-12	3/4"	25	23	.865"(22.0mm)	1.122"(28.5mm)	1.2"	6.7	50	792818
CLL-13	1"	32	29	1.087"(27.6mm)	1.358"(34.5mm)	1.4"	9.1	50	793816
CLL-14	1-1/4"	40	36	1.420"(36.0mm)	1.673"(42.5mm)	2.4"	11.0	50	794816
CLL-15	1-1/2"	50	48	1.850"(47.00mm)	2.145"(54.5mm)	2.8"	16.0	50	795816
CLL-17	2-1/2"	70	70	2.645"(67.0mm)	3.150"(80.0mm)	6.3"	32.0	30	79686
CLL-350	3-1/2"	95	95	3.600"(91.5mm)	4.170"(106mm)	8.3"	52.0	30	79886

\*Reels available. Consult factory.

See [Corrlok Information Page](#)

## TYPE - CLL

This lightweight version provides many of the same qualities of Type CL but with improved flexibility.

**UL** Recognized Component File #E174249 600 Volt, 105 Degrees ©, Vertical Flame, Liquidtight, UV and Impact Tested.

### Fittings:

To be used with the Corrllok® connectors of the Corrllok® System

### Fitting Pull-Out:

40 lbs. (1/2" and larger)

### Material:

Halogen Free Nylon 6

### STANDARD COLORS:

Black. [Other colors available upon request](#)

**WORKING TEMPERATURES:**

-40°C to 105°C

**Flexibility:** [See the Flexibility Comparison Guide](#)

**Plastic Used:** **NYLON** [See the Chemical Resistance Guide](#)

High Mech. Strength	Listed For Direct Burial	Halogen Free	Low Fire Hazard	Accepts Standard Liquidtight Fittings	Self Extinguish	EMI/RFI Shielding	Oil Resistance	Acid Resistance
		X			X		X	

---

® Electri-Flex Company 1-800-323-6174