



TECHSPRAY®

Technical Data Sheet

Economy Duster

1673

Techspray dusters blow away dust, microscopic contaminants, lint, metallic oxide deposits and other soils that can cause heat buildup or shorts in sensitive electronics.



Economical HFC-152a duster

Economical HFC152a based duster. Note: not for use on powered electrical equipment, on hot surfaces, and around open flames or sparks.

- Best value — 30% more volume
- Lower global warming potential — 10% of HFC-134a
- Non-ozone depleting
- Moisture free
- Zero residue
- Safe on plastics
- VOC exempt
- Velocity – 11.4 m/s

Product Packaging

1673-10S
Economy Duster
10 oz
12 units/case



Instructions

Can must be held in an upright position when spraying. Do not tilt can more than 40 degrees during spraying operation or shake during use. Before use, press actuator to clear valve of any liquid product. Use short burst to prevent cooling of can. Note: Do not use on photographic negatives without first clearing valve.

Chemical & Physical Properties

Appearance	Colorless gas
Odor	Faint ethereal odor
Flash Point	< -50°C (-58°F)
VOC (EPA)	0%
VOC (CARB)	0%
Boiling Point	-25°C (-13°F)
Density	





Chemical Composition

CHEMICAL NAME	CAS #
1,1-difluoroethane (HFC-152a)	75-37-6

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe

ITW Contamination Control BV
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.