Mini Jumper 2Way, 2.54mm

multicomp

RoHS Compliant



Features:

• Double tuning fork type contact guarantees high reliability 2.54mm pitch Low-profile mini. Type Males to 0.64mm sg. Posts

Specifications:


No. of Positions
Pitch Spacing
Connecting Termination
Current Rating
Contact Resistance
Insulation Resistance
Dielectric Withstanding Voltage

Material:


Insulator Terminal : 100MΩ Min. : AC 650V rms at sea level

: 30% Glass fiber + P.B.T.

: Phosphor Bronze Finishing Gold plated



: 2 : 2.54mm : Jumper : 3A Max. : 20mΩ Max.



Dimensions : Millimetres

Part Number Table

Description	Part Number
Mini Jumper, Open Type, 2Way, 2.54mm	SPC19807

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of use hors or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com

