






# **Wire Strippers/Cutters**

### Features:



# Wire Strippers/Cutters KLEIN-KURVE®

Additional Features:

- Easy-to-read markings.
- Precision shear-type blades.
- Cleanly shears 6-32 and 8-32 screws.





11055

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Screw Shearing	Weight (lbs.)
11053	blue/red	7-1/8" (181 mm)	6 – 12 AWG stranded (10 mm² – 2.5 mm²)	6-32 & 8-32	.34
11055	blue/yellow	7-1/8" (181 mm)	10 – 18 AWG solid (4.0 mm <sup>2</sup> – .75 mm <sup>2</sup> ) & 12 – 20 AWG stranded (2.5 mm <sup>2</sup> – .50 mm <sup>2</sup> )	6-32 & 8-32	.34
11057	blue/red	7-1/8" (181 mm)	20 - 30 AWG solid (.50 mm <sup>2</sup> 14 mm <sup>2</sup> ) & $22 - 32$ AWG stranded (.34 mm <sup>2</sup> 05 mm <sup>2</sup> )	6-32 & 8-32	.32

# **Dual NM Cable Strippers/Cutters KLEIN-KURVE**

Additional Features:

- 10/2, 12/2, and 14/2 stripping slots quickly remove outer jacket of Type NM-B nonmetallic-sheathed cable.
- Stripping holes easily remove insulation on 10, 12, and 14 AWG lead wire.
- Precision staggered blades for square, clean cuts on solid copper wire.
- Narrow nose fits into tight places.
- Precision shear-type blades for square, clean cuts on solid copper wire.











K1412

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM-B Cable	Screw Shearing	Weight (lbs.)
K1210	yellow/orange	7-3/4" (197 mm)	10 & 12 AWG solid (4.0 mm <sup>2</sup> & 2.5 mm <sup>2</sup> )	10/2 & 12/2	6-32 & 8-32	.43
K1412	yellow/white	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm <sup>2</sup> & 1.5 mm <sup>2</sup> )	12/2 & 14/2	6-32 & 8-32	.41

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock. AWARNING: Never use on or near live electrical circuits.

# **Dual NMD-90 Cable Strippers/Cutters**

Additional Features:

- Quickly removes outer jacket of Canadian NMD-90 Romex® Cable.
- Strips, cuts, and loops 12 & 14 AWG solid wires.
- Strips, cuts, and loops 14 & 16 AWG stranded wires.
- Cleanly shears 6-32 and 8-32 screws.
- Serrated nose bends, shapes and pulls wire.
- Double-dipped comfort grips with curved handles.



K1412CAN









Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NMD-90 Cable	Screw Shearing	Weight (lbs.)
K1412CAN	yellow/white	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm² & 1.5 mm²) 14 & 16 AWG stranded (1.5 mm² & 1.0 mm²)	12/2 & 14/2	6-32 & 8-32	.41

Romex® is a registered trademark of Southwire Company.

QTR-Turn™ NM Cable Stripper/Cutter KLEIN-KURVE®

Additional Features:

- Exclusive QTR-Turn™\* technology to quickly remove outer jacket of NM Cable.
- Strips, cuts, and loops 12 & 14 AWG solid wire.
- Cleanly shears 6-32 and 8-32 screws.
- Serrated nose bends, shapes, and pulls wire.





K1412-3

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM Cable	Screw Shearing	Weight (lbs.)
K1412-3	yellow/blue	7-3/4" (197 mm)	12 & 14 AWG solid (2.5 mm <sup>2</sup> & 1.5 mm <sup>2</sup> )	12/3 & 14/3	6-32 and 8-32	.41

QTR-Turn<sup>TM</sup> is a trademark of Stride Tool Incorporated.

# **Bent Nose NM Cable Stripper/Cutters**

Additional Features:

- Patented 90° bent nose for easy work in confined spaces.
- Quickly removes outer jacket of Romex® Cable.
- Strips, cuts, and loops 10, 12 or 14 AWG solid wires.
- Cleanly shears 6-32 & 8-32 screws.
- Serrated nose bends, shapes, and pulls wire.



K90-12/2

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Type NM Cable	Screw Shearing	Weight (lbs.)
K90-10/2	yellow/orange	7-3/8" (187 mm)	10 AWG solid (4.0 mm²)	10/2	6-32 and 8-32	.41
K90-12/2	yellow/yellow	7-3/8" (187 mm)	12 AWG solid (2.5 mm²) & 18 AWG stranded (1.0 mm²)	12/2	6-32 and 8-32	.41
K90-14/2	yellow/white	7-3/8" (187 mm)	14 AWG solid (1.5 mm²) & 18 AWG stranded (1.0 mm²)	14/2	6-32 and 8-32	.41

Romex<sup>®</sup> is a registered trademark of Southwire Company.

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.





# **Wire Strippers/Cutters**

# Features: Textured handles provide a firm, comfortable grip. **Spring loaded for** self-opening action. Wire looping and bending holes. KLEIN TOOLS **Precision-ground** stripping holes for easy removal of insulation. **Black-oxide finish** resists corrosion. Easy-to-read wire gauge markings on both sides for stripping in either direction.

## **Wire Strippers/Cutters**

Additional Features:

- Compact, lightweight wire-stripping and cutting tools.
- Narrow nose fits into tight places.
- Hardened steel with precision ground stripping holes.
- Do not use for cutting steel wire or bolts.

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
11045	yellow	6-1/4" (159 mm)	10 – 18 AWG solid (4.0 mm <sup>2</sup> – .75 mm <sup>2</sup> )	.27
11046	red	6-1/4" (159 mm)	16 - 26 AWG stranded (1.0 mm²14 mm²)	.27
11047	yellow	6-1/4" (159 mm)	22 - 30 AWG solid (.34 mm <sup>2</sup> 05 mm <sup>2</sup> )	.27
11049	red	6-1/4" (159 mm)	8 – 16 AWG stranded (6 mm² – 1.0 mm²)	.27



11045

# **Dual-Wire Stripper/Cutter**

Additional Features:

- Strips two wires in a single motion.
- Paired stripping holes for 14 and 12 AWG solid wire.
- One stripping hole for 10 AWG solid wire.
- Shear-type cutting blades for square, clean cuts.
- Narrow nose fits into tight places.
- Hardened steel with precision ground stripping holes.

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
11048	yellow	6-1/4" (159 mm)	10, 12, 14 AWG solid (4.0 mm², 2.5 mm², 1.5 mm²)	.27







11048

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Will NOT protect against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.



### Wire Stripper/Cutter – Solid and Stranded Wire

- Strips six standard wire sizes without nicking wire.
- Scissors action of 1/2" (13 mm) wide cutter makes clean cuts with little effort.
- Serrated nose jaws to bend, shape or pull wire; holes for looping wire ends.
- Spring-loaded for self-opening action.
- Comfortable, plastic-covered handles.

Cat. No.	Overall Length	Strips and Cuts	Handle Color	Weight (lbs.)
1011	6-1/8" (156 mm)	10 - 20 AWG solid & stranded (4.0 mm²50 mm²)	blue	.23



## Adjustable Wire Strippers/Cutters — Solid and Stranded Wire

- A handy, light, compact tool for stripping insulation.
- Convenient hole for looping or bending wire.
- Black-oxide finish with plastic-dipped handles.

1003

- Cuts, strips, and loops 12-26 solid and stranded wire.
- Adjustable slide stop with set screw for repeat stripping work.

5" (127 mm)

Cat. No.	Hold-Open Spring	Overall Length	Strips and Cuts	Handle Color	Weight (lbs.)
1004	yes	5" (127 mm)	12 – 26 AWG solid & stranded (2.5 mm² – 0.14 mm²)	yellow	.18

 $(2.5 \text{ mm}^2 - 0.14 \text{ mm}^2)$ 

12 - 26 AWG solid & stranded vellow





.14

# Adjustable Wire Stripper – Solid and Stranded Wire

- Simply dial desired wire size for fast, easy stripping.
- Adjustable tool makes short work of cutting and stripping operations.
- Finely honed nose cutter easily gets into tight areas.
- Wire gauge dial sets stripping dies to proper size, helps prevent nicked wire.
- Black-oxide finish with plastic-dipped handles.
- Spring-loaded design tool opens automatically after each action.


Cat. No.	Overall Length	Strips and Cuts	Handle Color	Weight (lbs.)
74007	5-1/8" (130 mm)	12 – 24 AWG solid & stranded (2.5 mm² – .25 mm²)	yellow	.15



### **Katapult® Wire Stripper – 8-22 AWG** KATAPULT

- Quick and easy 8-22 AWG wire stripping.
- Compound action wire stripping: grip and strip via single action squeezing motion.
- Precision machined stripping holes easily remove jacket insulation without damaging the wire.
- Remove up to 1" (24mm) in length of the insulation layer (jacket layer) in a single step.
- Tension loaded wire-grip gently holds the cable in place while retaining the cable geometry.
- Recoil spring design returns tool to ready position upon cycle completion.
- Cast alloy chassis with heavy-duty Ecoat finish for corrosion resistance and durability.
- Katapult® Coaxial Cable Stripper RG6 (Cat. No. VDV110-045) is also available.
- Additional precision machined steel cutting blades available.

Cat. No.	Color	Strips	Overall Length	Weight (oz.)					
11063	blue/black	8-22 AWG (6 mm2 – .34 mm2)	6.6" (168 mm)	12.1					
Wire Stop/Gauge									
11081	6	adjustable wire stop		.01					



All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock AWARNING: Never use on or near live electrical circuits

**AWARNING:** Always wear approved eve protection.





11063

# **Combination Wire-Stripping and Cutting Tools**

## **Multi-Purpose 6-in-1 Tool**

- Cleanly shears bolts.
- Easily cuts and strips wire.
- Measures stud sizes.
- Gauges wire sizes.
- Crimps insulated terminals.
- Plastic-covered cushioned handles for comfort.



1000

Cat. No.	Overall Length	Strips and Cuts	Bolt Sizes	Handle Color	Weight (lbs.)
1000	7-3/4" (197 mm)	10 – 22 AWG (4.0 mm² – .34 mm²)	4-40, 6-32, 8-32, 10-24, 10-32	red	.44

## **Multi-Purpose Electrician's Tool - 8-22 AWG**

- Two wire cutters—one at tip, the other halfway back near stripping holes—double the utility of this tool.
- Color-coded crimping dies for 10-22 AWG insulated and non-insulated terminals.
- Cleanly shears bolts.
- Pivot nut adjusts tension.
- Wire-looping holes near tip.
- Full-sized, plastic-covered cushioned handles for comfort.



1001

1010



CLEIN TOOLS 1771

Cat. No.	Overall Length	Strips and Cuts	Bolt Sizes	Handle Color	Weight (lbs.)
1001	8-1/2" (216 mm)	8 – 18 AWG solid (6.0 mm² – 1.0 mm²) 10 – 22 AWG stranded (4.0 mm² – .34 mm²)	4-40, 6-32, 8-32, 10-24, 10-32	red	.47

## **Long-Nose Multi-Purpose Tool**

- Easily cuts and strips wire.
- Narrow, serrated pliers nose to pull, loop, and bend wire.
- Long, curved cutting blade.
- Cutters and strippers are in front of the pivot for maximum ease-of-use in reaching into tight places.
- Crimps insulated and non-insulated terminals and 7 to 8 mm ignition terminals.
- Cleanly shears bolts.
- Plastic-covered cushioned handles for comfort.

Cat. No.	Overall Length	Bolt Sizes	Strips and Cuts	Connectors	Handle Color	Weight (lbs.)
1010	8-1/4" (210 mm)	4-40, 5-40, 6-32, 8-32, 10-32, 10-24	10 – 22 AWG (4.0 mm <sup>2</sup> – .34 mm <sup>2</sup> )	10 – 22 gauge	blue	.43

# Trip-Saver®

- Unique multi-tool addresses the special needs of electricians and maintenance professionals while providing many other features handy on any job.
- Compact, lightweight, and very sturdy.
- Produced from high-carbon, rust-resistant stainless steel.
- Specially designed locking "L" handle snaps securely into the "L" channel, locking the fully opened blade or implement in place during use.
- Features the following: Needle-Nose Pliers, Beveled Wire Cutter, Toothed Pipe Grippers, Files (coarse and fine), 5-Slot Wire Stripper (10-18) AWG, Wire-Looping Hole, Scraper, Awl/Reamer, Serrated Sheepsfoot Knife, Clip-Point Knife, Standard/Metric Ruler, Drywall Saw, Locking "L" Handle, #1 and #2 Phillips Hex Bits, Small-Slotted Hex Bit, Large-Slotted Hex Bit, 1/4" Socket Adapter, Lanyard Hole, Nylon Pouch.



1016

ı	Cat. No.	Overall Length	Weight (lbs.)
	1016	5-3/4" (143 mm)	.95

AWARNING: Close handles to lock blade in place before use.

All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock **AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.



48

## **NM Cable Ripper**

- Easy-to-use cable ripper.
- Slit the outer jacket of Romex® cable (all sizes) and other nonmetallic (type NM) sheathed cable.
- Measure conductor wire gauge.



74017

Cat. No.	Overall Length	Slits	Measures Wire Gauge	Weight (lbs.)
74017	4" (102 mm)	all sizes of Romex <sup>®</sup> and NM	8 – 14 AWG (6 mm <sup>2</sup> – 1 mm <sup>2</sup> )	.08

Romex<sup>®</sup> is a registered trademark of Southwire Company.

# **Crimping Tools Crimping/Cutting Tools –**

- **Non-Insulated/Insulated Terminals** Crimping die marked for insulated and
- non-insulated solderless terminals and connectors.
- Tapered nose design for working in confined spaces.
- Specially hardened wire cutter in nose.
- Hot-riveted joint for smooth action and no handle wobble.



Cat. No.	Handle Color	Crimps	Overall Length	Weight (lbs.)		
1005	red	10 – 22 AWG	9-3/4" (248 mm)	.80		
Journey	Journeyman Series – Dual-material handles					
J1005	red/black	10 – 22 AWG	9-3/4" (248 mm)	.84		

### **Crimping/Cutting Tool – Non-Insulated Terminals**

- Designed for crimping non-insulated solderless terminals and connectors.
- Specially hardened wire cutter in nose.
- Tapered nose for working in confined spaces.
- Plastic-dipped cushioned handles for comfort.



Cat. No.	Handle Color	Crimps	Overall Length	Weight (lbs.)
1006	black	10 – 22 AWG	9-3/4" (248 mm)	.85

# **Large Crimp Tool – Compound-Action**

- Crimps #6-4/0 AWG battery lugs and terminals.
- Ultra-comfortable hand grips for easy use.
- All-in-one, integral crimp nest. No removable parts or rotating dies.
- High-leverage handles and compound-action mechanism for superior mechanical advantage.
- Adjustment screw allows user to control crimp depth.

Cat. No.	Crimps	Handle Color	Overall Length	Weight (lbs.)
2006	#6 – 4/0 AWG battery lugs and terminals	red	19-1/2" (495 mm)	3.80



All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock. **AWARNING:** Never use on or near live electrical circuits.

**AWARNING:** Always wear approved eye protection.





2006

# **Ratcheting Crimpers**

# Full-Cycle Ratcheting Crimper – Insulated Terminals

- Crimps insulated terminals in wire sizes 22-16 (front cavity), 16-14 (middle cavity), and 12-10 (rear cavity).
- Color-coded wire size markings.
- Compound lever-action of narrow-span handles puts more crimping power into each squeeze.
- Comfort-grip plastic handles.



T1715

Cat. No.	Handle Color	Crimps	Overall Length	Weight (lbs.)
T1715	black	10 – 22 AWG	9" (229 mm)	1.05

# **Compound-Action Ratcheting Crimper – Insulated Terminals**

- Compound-action tool crimps 10-22 AWG insulated terminals to meet or exceed MIL-SPEC pull-out tests.
- Built-in ratchet with safety release assures uniform crimps every time.
- Compound lever-action of narrow-span handles puts more crimping power into each squeeze.
- Special locator quickly positions terminal for double crimp.
- Comfort-grip plastic handles.



T1710

Cat. No.	Handle Color	Crimps	Overall Length	Weight (lbs.)
T1710	black	10 – 22 AWG	9" (229 mm)	1.29

### **Full-Cycle Coax Ratcheting Crimper**

- Crimps hex-configuration (in dimensions across flats) coaxial connectors.
- Dimensions clearly marked for quick identification.
- Front cavity (.262") for RG-59.
- Middle cavity (.324") for RG-5, 6, 21, 143, 212, 222, and 304, also for Belden 8281, 9231 and 9141.
- Rear cavity (.384") for RG-8, 9, 11, 149, and 213.
- Ratchet release allows quick removal of incorrectly placed connector prior to completing crimp.
- Compound lever-action of narrow-span handles puts more crimping power into each squeeze.
- Comfort-grip plastic handles.
- Tool jaws will not open until the crimp is completed.
  They release and open automatically when crimp is done.



T1720

Cat. No.	Handle Color	<b>Hex Configurations</b>	Overall Length	Weight (lbs.)
T1720	black	front cavity .262"; middle cavity .324"; rear cavity .384"	9" (229 mm)	1.30



All dimensions are in inches and (millimeters).

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**AWARNING:** Never use on or near live electrical circuits.