Low Power Bipolar Transistor multicomp







Pin Configuration:

- 1. Collector
- 2. Base
- 3. Emitter

Features:

- · PNP Silicon Planar Switching Transistor
- · General Purpose Switching and Amplifier Applications

Absolute Maximum Ratings

Description	Symbol	Value	Unit	
Collector-Emitter Voltage	V _{CEO}	40		
Collector-Base Voltage	V _{CBO}	40	V	
Emitter-Base Voltage	V _{EBO}	5		
Collector Current Continuous	I _C	200	mA	
Power Dissipation at T _a = 25°C Derate above 25°C	D	625 5	mW mW/°C	
Power Dissipation at T _c = 25°C Derate above 25°C	P _D	1.5 12	W mW/°C	
Operating and Storage Junction Temperature Range	T _j , T _{stg}	-55 to +150	°C	

Thermal Resistance

Junction to Case	R _{th (j-c)}	125	°C/W
Junction to Ambient	R _{th (j-a)}	200	C/VV



Low Power Bipolar Transistor multicomp



Electrical Characteristics ($T_a = 25$ °C unless otherwise specified)

Description	Symbol	Test Condition	2N3906	Unit
Collector-Emitter Voltage	V _{CEO} *	$I_{C} = 1\text{mA}, I_{B} = 0$ $I_{C} = 10\mu\text{A}, I_{E} = 0$ >40		V
Collector-Base Voltage	V_{CBO}			
Emitter-Base Voltage	V _{EBO}	$I_{E} = 10 \mu A, I_{C} = 0$	>5	
Collector-Cut off Current	I _{CEX}	V - 20V V - 2V	4 F0	A
Emitter-Cut off Current	I _{BL}	$V_{CE} = 30V, V_{EB} = 3V$	<50	nA
DC Current Gain	h _{FE} *	$\begin{split} I_{C} &= 0.1 \text{mA}, V_{CE} = 1 \text{V} \\ I_{C} &= 1 \text{mA}, V_{CE} = 1 \text{V} \\ I_{C} &= 10 \text{mA}, V_{CE} = 1 \text{V} \\ I_{C} &= 50 \text{mA}, V_{CE} = 1 \text{V} \\ I_{C} &= 100 \text{mA}, V_{CE} = 1 \text{V} \end{split}$	>60 >80 100 - 300 >60 >30	-
Collector Emitter Saturation Voltage	V _{CE (sat)} *	I _C = 10mA, I _B = 1mA	<0.25 <0.4	V
Base Emitter Saturation Voltage	V _{BE (sat)} *	I _C = 50mA, I _B = 5mA	0.65 - 0.85 <0.95	

Small Signal Characteristic

Transistors Frequency	f _T	I _C = 10mA, V _{CE} = 20V, f = 100MHz	>250	MHz
Output Capacitance	C _{ob}	V _{CB} = 5V, I _E = 0, f = 100kHz	<4.5	F
Input Capacitance	C _{ib}	$V_{BE} = 0.5V, I_{C} = 0, f = 100kHz$	<10	pF
Small Signal Current Gain	h _{fe}	All f = 1kHz I _C = 1mA, V _{CE} = 10V	100 - 400	-
Input Impedance	h _{ie}		2 - 12	kΩ
Output Admittance	h _{oe}		3 - 6	μΩ
Voltage Feedback Ratio	h _{re}		1 - 10	× 10 ⁻⁴
Noise Figure	NF	$I_C = 100\mu\text{A}, V_{CE} = 5\text{V}$ $R_s = 1\text{k}\Omega$ $f = 10\text{Hz} \text{ to } 15.7\text{kHz}$	<40	dB

Switching Time


Delay Time	t _d	$V_{CC} = 3V, V_{BE} = 0.5V$	<35	
Rise Time	t _r	I _C = 10mA, I _{B1} = 1mA	7	no
Storage Time	t _s	$V_{CC} = 3V$, $I_{C} = 10$ mA	<225	ns
Fall Time	t _f	I _{B1} = I _{B2} = 1mA	<75	

^{*}Pulse Condition : Pulse Width = 300µs, Duty Cycle = 2%.




Low Power Bipolar Transistor multicomp





Dimensions	Min.	Max.
А	4.32	5.33
В	4.45	5.2
С	3.18	4.19
D	0.41	0.55
Е	0.35	0.5
F	5	0
G	1.14	1.4
Н		1.53
K	12.7	-

Dimensions: Millimetres



Pin Configuration:

- 1. Collector
- 2. Base
- 3. Emitter

Part Number Table

Description	Part Number
Transistor, PNP, TO-92	2N3906

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any windout notice and the spaces are spaces. The information supplied to be accurate but the spaces and the spaces are spaces and the spaces are spaces. The spaces are spaces are spaces are spaces and the spaces are spaces and the spaces are spaces and the spaces are spaces. The spaces are spaces are spaces are spaces and the spaces are spaces and the spaces are spaces and the spaces are spaces. The spaces are spaces are spaces are spaces are spaces and the spaces are spaces and the spaces are spaces. The spaces are spaces are spaces are spaces are spaces and the spaces are spaces and the spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces. The spaces are spaces. The spaces are spaces are spaces are spaces are spaces are spaces are spaces are

www.element14.com www.farnell.com www.newark.com

