



## LED Lamp, On/Off Switch or Movement Sensor

### Lamp LED 025



- Wide voltage range
- Integrated power unit
- Daisy chain
- Long-lived and maintenance-free by LED technology
- Magnet or screw fixing
- On/off switch or movement sensor

The lamp series LED 025 is suitable for all types of panels and enclosures, especially where space is at a premium. The lamps have a very long service life thanks to the use of LED technology. They are available with powerful non-slip rubberized magnets allowing them to be quickly positioned in any steel enclosure. Alternatively they can be fixed mechanically. The power output allows up to 10 lamps to be connected to each other (daisy chain). Both the power input and output connectors snap lock into their sockets. With the integrated power unit and the plugs the lamp can quickly be connected.

### Technical Details

>> [Download PDF](#)

<b>Power consumption</b>	max. 5W
<b>Luminosity</b>	290Lm at 120° (870Lm at 360° or equivalent 75W light bulb)
<b>Lamp type</b>	LED, angle of radiation 120°
	light color: daylight, color temperature: 6,500K
<b>Service life</b>	60,000h at +20°C (+68°F)
<b>Connection</b>	2-pole connector with snap lock
	AC: max. 2.5A / 240VAC, color: white
	DC: max. 2.5A / 60VDC, color: blue
<b>Mounting</b>	magnet fixing or screw fixing (M5), torque 2Nm max., 250mm centers
<b>Casing</b>	plastic, transparent
<b>Dimensions</b>	see drawings
<b>Operating/Storage temperature</b>	-30 to +60°C (-22 to +140°F) / -40 to +85°C (-40 to +185°F)
<b>Operating/Storage humidity</b>	max. 90% RH (non-condensing)
<b>Protection type/Protection class</b>	IP20 / II (double insulated)
<b>Approvals</b>	UL File No. E234324, VDE

**Important note:** Connectors and cables for electrical connection are not included in the delivery. These parts can be ordered separately (see Accessories, next page). Sets, consisting of lamp and accessories, are available on request.

[To top](#)

Art. No. Magnet fixing	Art. No. Screw fixing	Operating voltage	Switch	Weight (approx.)
<b>02540.0-00</b>	02540.0-01	100-240VAC, 50/60Hz (min. 90VAC, max. 265VAC)	on/off light switch	0.2kg
<b>02540.1-00</b>	02540.1-01	24-48VDC (min. 20VDC, max. 60VDC)	on/off light switch	0.2kg
<b>02541.0-00</b>	02541.0-01	100-240VAC, 50/60Hz (min. 90VAC, max. 265VAC)	PIR movement sensor <sup>1</sup>	0.2kg
<b>02541.1-00</b>	02541.1-01	24-48VDC (min. 20VDC, max. 60VDC)	PIR movement sensor <sup>1</sup>	0.2kg

<sup>1</sup> approx. 5 min. fixed switch-on duration

[To top](#)

## Connection cable with female connector and open end

Art. No.	Model	Length	Voltage type	Color	Use for	Approvals <sup>2</sup>
<b>244356</b>	connection cable 2 x 1.5mm <sup>2</sup> with female connector	2.0m	AC	connector: white; cable: white	power input	VDE
<b>244357</b>	connection cable 2 x AWG 16 with female connector	2.0m	AC	connector: white; cable: white	power input	VDE + UL
<b>244360</b>	connection cable 2 x 1.5mm <sup>2</sup> with female connector	2.0m	DC	connector: blue; cable: white	power input	VDE
<b>244361</b>	connection cable 2 x AWG 16 with female connector	2.0m	DC	connector: blue; cable: white	power input	VDE + UL

<sup>2</sup> applies only to the individual components (cable and connectors)

[To top](#)

## Extension cable with 2 connectors for daisy chain connection

Art. No.	Model	Length	Voltage type	Color	Use for	Approvals <sup>2</sup>
<b>244358</b>	extension cable 2 x 1.5mm <sup>2</sup> with 2 connectors	1.0m	AC	connectors: white; cable: white	daisy chain	VDE
<b>244359</b>	extension cable 2 x AWG 16 with 2 connectors	1.0m	AC	connectors: white; cable: white	daisy chain	VDE + UL
<b>244362</b>	extension cable 2 x 1.5mm <sup>2</sup> with 2 connectors	1.0m	DC	connectors: blue; cable: white	daisy chain	VDE
<b>244363</b>	extension cable 2 x AWG 16 with 2 connectors	1.0m	DC	connectors: blue; cable: white	daisy chain	VDE + UL


<sup>2</sup> applies only to the individual components (cable and connectors)

[To top](#)

## Female / Male connectors

Art. No.	Model	Voltage type	Color	Use for	Approvals
<b>264057</b>	female connector	AC	white	power input	VDE + UL
<b>264058</b>	male connector	AC	white	power output	VDE + UL
<b>264059</b>	female connector	DC	blue	power input	VDE + UL
<b>264060</b>	male connector	DC	blue	power output	VDE + UL

## Technical Drawing



Lamp Series LED 025

[To top](#)