


Isolation (115VAC to 115VAC) 171 Series

Plug-In




Features

- Primary 115VAC, 50/60 Hz., Secondary 115VAC
- Provides complete circuit isolation.
- Electrostatic shield between primary & secondary to greatly attenuate surges and noise.
- Hi-pot tested to 2 KV RMS.
- Circuit breaker in primary.
- Standard 3-wire, grounded plug & receptacle.
- Input (primary) connected to 5 foot long cord & standard North American plug (NEMA 5-15P).
- Output (secondary) connected to 1 foot long "pig tail" cord, 3-wire, standard North American grounded receptacle (NEMA 5-15R).
- North American Mark of Safety - C UL & UL listed (File #E211544)
- Indoor use only
- **Remember** - These units do NOT convert line frequency

Accessories

- International Grounded Adaptor Plugs



Part No.	Capacity VA	Leakage Current μ A	Full Load Efficiency	Full Load Total		Capacitance Between Windings @ 1Khz	Circuit Breaker (Amps)	Dimensions					Weight Lbs
				Harmonic Distortion	Surge/ Noise Suppression dB			A	B	C	D	E	
171A	100	72.12 μ A	89%	0.21%	-37.7 dB	15 pF	1	3.80	5.06	4.68	3.00	3.38	6.5
171B	200	47.52 μ A	93%	0.195 %	-37.15 dB	15 pF	2	3.80	5.56	4.68	3.00	3.88	8
171C	300	54.92 μ A	94%	0.24%	-34.32 dB	20 pF	3	3.80	6.06	4.68	3.00	4.38	11
171E	500	59.66 μ A	93%	0.18%	-37.18 dB	20 pF	5	3.80	7.06	4.68	3.00	5.38	14
171F	750	70.07 μ A	95%	0.24%	-32.27 dB	20 pF	7	4.40	8.70	5.39	3.50	6.78	30
171G	1000	70.58 μ A	95%	0.109%	-35 dB	40 pF	10	5.28	7.75	6.38	4.25	4.38	34.5

Data subject to change without notice

© 2016. Hammond Manufacturing Ltd. All rights reserved.