


Potential Transformer Instrument *EX-HX-VT Series*



Features

- Used (with 150 Volt full scale A.C. voltmeters) to measure the voltage of 240, 480 or 600 VAC systems.
- Primary insulated for 4.0 KV rms test, suitable for L.V. switchgear and motor control use.
- 50/60 Hz. operation.
- Open construction - "Type H".
- CSA certified (209651).
- The nominal line voltages of 240 and 480 volts may be exceeded by 25% for 60 Hz. operation.
- Insulation system 55 degree C rise, Class 105.



| Part No. | Nominal Line | Ratio | Accuracy | Thermal | Overall Dimensions | | | Mounting Centers | | Mounting Slot | | Ship Wt. | |
|--------------|--------------|-------------|----------|-----------|--------------------|------|------|------------------|------|---------------|------|----------|-----|
| | Voltage | Pri. / Sec. | % | VA Rating | A | B | C | D | E | G | H | Lb. | |
| VT55A | 240 | 240:120 | 1.2 | 0-8 | 50 | 3.00 | 3.25 | 2.56 | 2.50 | 2.50 | 0.22 | 0.44 | 3 |
| HX54A | 240 | 240:120 | 1.2 | 0-20 | 100 | 3.75 | 4.00 | 3.13 | 3.13 | 3.13 | 0.22 | 0.44 | 6.6 |
| VT56A | 347 | 347:120 | 1.2 | 0-8 | 50 | 3.00 | 3.25 | 2.56 | 2.50 | 2.50 | 0.22 | 0.44 | 3 |
| VT57A | 480 | 480:120 | 1.2 | 0-8 | 50 | 3.00 | 3.25 | 2.56 | 2.50 | 2.50 | 0.22 | 0.44 | 3 |
| HX74A | 480 | 480:120 | 1.2 | 0-20 | 100 | 3.75 | 4.00 | 3.13 | 3.13 | 3.13 | 0.22 | 0.44 | 6.6 |
| VT59A | 600 | 600:120 | 1.2 | 0-8 | 50 | 3.00 | 3.25 | 2.56 | 2.50 | 2.50 | 0.22 | 0.44 | 3 |
| HX94A | 600 | 600:120 | 1.2 | 0-20 | 100 | 3.75 | 4.00 | 3.13 | 3.13 | 3.13 | 0.22 | 0.44 | 6.6 |

Data subject to change without notice