# **Stacked Coin Type**

Series: RF



# **Features**

● Endurance: +85 °C 2000 h Can be discharged mA current


RoHS compliant

# Recommended applications

- Backup of data/RTC of base station, electronic meter, and industrial equipment
- For assist of rapid load change

Specifications							
Category temp. range	−25 °C to +85 °C						
Maximum operating voltage	5.5 V.DC						
Nominal capacitance	0	.1 F	0.68 F, 1.0 F				
Characteristics at	Capacitance change	±30 % of initial measured value at +20 °C (at -25 °C)					
low temperature	Internal resistance	≤5 times of initial measured value at +20 °C (at -25 °C)					
	After 2000 hours application of maximum operating voltage at +85 °C						
Endurance	Capacitance change	±30 % of initial measured value at 20 °C					
	Internal resistance	150 Ω or less (0.1 F)					
		40 Ω or less (0.68 F, 1.0 F)					
	After 2000 hours storage at +85 °C without load (voltage)						
Shelf life	Capacitance change	Capacitance change shall meet the specified limits for Endurance					
	Internal resistance	Internal resistance shall meet the specified limits for Endurance					

# **Dimensions in mm(not to scale)**



# **Characteristics list**

Category temp. range (°C)	Maximum operating voltage (V.DC)	Capacitance (F)	i folerance	Internal resistance (Initial specified value) (Ω) at 1 kHz	Recommended *1 discharge current (mA)		Mass (Reference value)	Min. packaging q'ty (pcs)
-25 to +85	5.5	0.1	0.080 to 0.180	≤ 75	3 or less	EECRF0H104	3.3	200
		0.68	0.544 to 1.224	≤ 20	20 or less	EECRF0H684	10.0	100
		1.0	0.8 to 1.8	≤ 20	20 or less	EECRF0H105	10.0	100

<sup>\*1</sup> The recommended discharge current is a reference value. Please design your equipment(circuit) in consideration of IR drop.

Do not use reflow soldering. Please refer to the page of "Application guidelines".