



## Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 13

LOCTITE RA 10 SN62BAS86 7K known as SN62RA10BAS86

SDS No. : 175645  
V004.3

Revision: 31.05.2015  
printing date: 15.08.2016

Replaces version from: 14.05.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE RA 10 SN62BAS86 7K known as SN62RA10BAS86

#### Contains:

Lead  
Rosin

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Solder Paste

#### 1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA  
Henkelstr. 67  
40191 Düsseldorf

Germany

Phone: +49 (211) 797-0

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Toxic to reproduction	Category 1A
H360FD May damage fertility. May damage the unborn child.	
Specific target organ toxicity - repeated exposure	Category 1
H372 Causes damage to organs through prolonged or repeated exposure.	
Acute hazards to the aquatic environment	Category 3
H412 Harmful to aquatic life with long lasting effects.	

#### 2.2. Label elements

##### Label elements (CLP):

**Hazard pictogram:****Signal word:**

Danger

**Hazard statement:**

H317 May cause an allergic skin reaction.  
 H360FD May damage fertility. May damage the unborn child.  
 H372 Causes damage to organs through prolonged or repeated exposure.  
 H412 Harmful to aquatic life with long lasting effects.

**Supplemental information**

Restricted to professional users.

**Precautionary statement:****Prevention**

P201 Obtain special instructions before use.  
 P261 Avoid breathing fume.  
 P273 Avoid release to the environment.  
 P280 Wear protective gloves/protective clothing.

**Precautionary statement:****Response**

P308+P313 IF exposed or concerned: Get medical advice/attention.  
 P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

**2.3. Other hazards**

Self classification: product testing according to Classification, Labelling and Packaging Regulation EC/1272/2008, Annex 1, Part 4.

This product contains modified rosin.

Contains lead which may harm your health. Lead can cause birth defects and other reproductive harm.

Regulations forbid the use of lead solder in any private or public drinking water supply system.

Do not heat above 500 °C

Avoid breathing fumes given out during soldering.

Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).

After handling solder wash hands with soap and water before eating, drinking or smoking.

Keep out of reach of children.

## SECTION 3: Composition/information on ingredients

**3.2. Mixtures****Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Tin 7440-31-5	231-141-8 01-2119486474-28	50- 60 %	
Lead 7439-92-1	231-100-4 01-2119510714-47	30- 40 %	Repr. 1 H360FD STOT RE 1 H372 Aquatic Acute 1 H400 Aquatic Chronic 1 H410
Rosin 8050-09-7	232-475-7 01-2119480418-32	5- 10 %	Skin Sens. 1 H317
Silver >= 99,9 % Ag in powder (< 1 mm) 7440-22-4	231-131-3	1- 5 %	Aquatic Acute 1 H400 Aquatic Chronic 1 H410 M factor: 1.000 M factor (Chron Aquat Tox): 1.000

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.

Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

Chronic overexposure to lead may result in damage to the blood forming, nervous, urinary and reproductive systems. Severe lead toxicity will cause sterility, abortion and neonatal mortality and morbidity.

Prolonged or repeated skin contact with silver and its salts may cause a blue-gray discoloration of the skin and mucous membranes that is irreversible (Argyria).

INGESTION: Nausea, vomiting, diarrhea, abdominal pain.

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

SKIN: Rash, Urticaria.

### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Suitable extinguishing media:**

water, carbon dioxide, foam, powder

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

### 5.2. Special hazards arising from the substance or mixture

High temperatures may produce heavy metal dust, fumes or vapours.

### 5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

Keep unprotected persons away.

Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not let product enter drains.  
Do not allow to enter the ground / soil.

**6.3. Methods and material for containment and cleaning up**

Scrape up spilled material and place in a closed container for disposal.  
Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage**

**7.1. Precautions for safe handling**

Avoid skin and eye contact.  
See advice in section 8  
Extraction is necessary to remove fumes evolved during reflow.  
When using do not eat, drink or smoke.  
Wash hands before breaks and immediately after handling the product.  
Avoid breathing fumes given out during soldering.  
Do not heat above 500 °C

Hygiene measures:

Good industrial hygiene practices should be observed.  
Do not eat, drink or smoke while working.  
After handling solder wash hands with soap and water before eating, drinking or smoking.

**7.2. Conditions for safe storage, including any incompatibilities**

Ensure good ventilation/extraction.  
Store in original container at temperatures 5-10°C.

**7.3. Specific end use(s)**

Solder Paste

<b>SECTION 8: Exposure controls/personal protection</b>
---------------------------------------------------------

**8.1. Control parameters****Occupational Exposure Limits**Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Tin 7440-31-5 [TIN (INORGANIC COMPOUNDS AS SN)]		2	Time Weighted Average (TWA):	Indicative	ECLTV
Lead 7439-92-1 [LEAD AND LEAD COMPOUNDS, OTHER THAN LEAD ALKYL (AS PB)]		0,15	Time Weighted Average (TWA):		EH40 WEL
Lead 7439-92-1 [INORGANIC LEAD AND ITS COMPOUNDS]		0,15	Time Weighted Average (TWA):		EU_OEL
Lead 7439-92-1 [LEAD AND ITS IONIC COMPOUNDS]			Biological Limit Value:		EU_OEL_II
Rosin 8050-09-7 [ROSIN-BASED SOLDER FLUX FUME]		0,05	Time Weighted Average (TWA):		EH40 WEL
Rosin 8050-09-7 [ROSIN-BASED SOLDER FLUX FUME]		0,15	Short Term Exposure Limit (STEL):		EH40 WEL
Silver 7440-22-4 [SILVER (METALLIC)]		0,1	Time Weighted Average (TWA):		EH40 WEL
Silver 7440-22-4 [SILVER, METALLIC]		0,1	Time Weighted Average (TWA):	Indicative	ECLTV
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, PARTICULATES]		10	Time Weighted Average (TWA):		EH40 WEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES]	150	474	Time Weighted Average (TWA):		EH40 WEL

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Lead 7439-92-1	aqua (freshwater)					6,5 µg/L	
Lead 7439-92-1	aqua (marine water)					3,4 µg/L	
Lead 7439-92-1	sediment (freshwater)				41 mg/kg		
Lead 7439-92-1	sediment (marine water)				164 mg/kg		
Lead 7439-92-1	soil				147 mg/kg		
Lead 7439-92-1	STP					1 mg/L	
Rosin 8050-09-7	aqua (freshwater)					0,005 mg/L	
Rosin 8050-09-7	aqua (marine water)					0,0005 mg/L	
Rosin 8050-09-7	sediment (freshwater)				108 mg/kg		
Rosin 8050-09-7	sediment (marine water)				10,8 mg/kg		
Rosin 8050-09-7	soil				21,4 mg/kg		
Rosin 8050-09-7	STP					1000 mg/L	

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Tin 7440-31-5	Workers	Dermal	Acute/short term exposure - systemic effects		133,3 mg/kg	
Tin 7440-31-5	Workers	Inhalation	Acute/short term exposure - systemic effects		11,75 mg/m3	
Tin 7440-31-5	Workers	Dermal	Long term exposure - systemic effects		133,3 mg/kg	
Tin 7440-31-5	Workers	Inhalation	Long term exposure - systemic effects		11,75 mg/m3	
Tin 7440-31-5	general population	Dermal	Acute/short term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	general population	Inhalation	Acute/short term exposure - systemic effects		3,476 mg/m3	
Tin 7440-31-5	general population	oral	Acute/short term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	general population	Dermal	Long term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	general population	Inhalation	Long term exposure - systemic effects		3,476 mg/m3	
Tin 7440-31-5	general population	oral	Long term exposure - systemic effects		80 mg/kg	
Rosin 8050-09-7	Workers	Inhalation	Long term exposure - systemic effects		176,32 mg/m3	
Rosin 8050-09-7	Workers	Dermal	Long term exposure - systemic effects		25 mg/kg bw/day	
Rosin 8050-09-7	general population	Inhalation	Long term exposure - systemic effects		52,174 mg/m3	
Rosin 8050-09-7	general population	Dermal	Long term exposure - systemic effects		15 mg/kg bw/day	
Rosin 8050-09-7	general population	oral	Long term exposure - systemic effects		15 mg/kg bw/day	

**Biological Exposure Indices:**

Ingredient [Regulated substance]	Parameters	Biological specimen	Sampling time	Conc.	Basis of biol. exposure index	Remark	Additional Information
Lead 7439-92-1 [LEAD AND ITS IONIC COMPOUNDS]	Lead	Blood			EU HCA2		

**8.2. Exposure controls:**

## Engineering controls:

Ensure adequate ventilation, especially in confined areas.

Extraction is necessary to remove fumes evolved during reflow.

## Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

**Skin protection:**

Wear suitable protective clothing.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	paste
	grey
Odor	mild
Odour threshold	No data available / Not applicable
pH	Not applicable
Initial boiling point	Not determined
Flash point	> 100 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	Not determined
Density	4,1500 g/cm <sup>3</sup>
( )	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	179,0 °C (354.2 °F)
Flammability	No data available / Not applicable
Auto-ignition temperature	186 °C (366.8 °F)
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	Not determined
Evaporation rate	No data available / Not applicable
Vapor density	Heavier than air
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Reacts with strong oxidants.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

**10.5. Incompatible materials**

None if used properly.

**10.6. Hazardous decomposition products**

Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Causes damage to organs through prolonged or repeated exposure.

**Inhalative toxicity:**

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs. Prolonged or repeated exposure to flux fumes may result in sensitisation in sensitive workers.

**Dermal toxicity:**

Prolonged or repeated skin contact with silver and its salts may cause a blue-gray discoloration of the skin and mucous membranes that is irreversible (Argyria).

**Skin irritation:**

Prolonged or repeated contact may cause skin irritation.

**Eye irritation:**

Solder pastes may be abrasive to the eyes and the fumes are irritating.

**Sensitizing:**

May cause an allergic skin reaction.

**Reproductive toxicity:**

May damage fertility. May damage the unborn child.

**Other remarks:**

Chronic overexposure to lead may result in damage to the blood forming, nervous, urinary and reproductive systems. Severe lead toxicity will cause sterility, abortion and neonatal mortality and morbidity.

**Acute oral toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Rosin 8050-09-7	LD50	2.800 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)
Silver >= 99,9 % Ag in powder (< 1 mm) 7440-22-4	LD50	> 2.000 mg/kg	oral		rat	

**Acute inhalative toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

**Acute dermal toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Rosin 8050-09-7	LD50	> 2.000 mg/kg	dermal		rat	OECD Guideline 402 (Acute Dermal Toxicity)

**Skin corrosion/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Rosin 8050-09-7	not irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

**Serious eye damage/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Rosin 8050-09-7	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

**Germ cell mutagenicity:**

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Rosin 8050-09-7	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)

**SECTION 12: Ecological information****General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**12.1. Toxicity****Ecotoxicity:**

Self classification: product testing according to Classification, Labelling and Packaging Regulation EC/1272/2008, Annex 1, Part 4.

Harmful to aquatic life with long lasting effects.

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Rosin 8050-09-7	LC50	> 1.000 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Rosin 8050-09-7	EC50	911 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Rosin 8050-09-7	EC50	> 100 mg/l	Algae	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	DIN 38412-09

**12.2. Persistence and degradability****Persistence and Biodegradability:**

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Rosin 8050-09-7		aerobic	36 - 46 %	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)

**12.3. Bioaccumulative potential / 12.4. Mobility in soil****Mobility:**

The product is insoluble and sinks in water.

**Bioaccumulative potential:**

Octanol/Water distribution coefficient: Not determined

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Rosin 8050-09-7	3 - 6,2					OECD Guideline 117 (Partition Coefficient (n- octanol / water), HPLC Method)

**12.5. Results of PBT and vPvB assessment**

Hazardous components CAS-No.	PBT/vPvB
Lead 7439-92-1	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Rosin 8050-09-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Silver >= 99,9 % Ag in powder (< 1 mm) 7440-22-4	Not fulfilling PBT (persistent/bioaccumulative/toxic) criteria

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:

Wherever possible unwanted solder pastes should be recycled for recovery of metal.

Dispose of as hazardous waste in compliance with local and national regulations.

Disposal of uncleaned packages:

Dispose of as unused product.

Waste code

06 04 05\* Waste containing other heavy metals

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

**SECTION 14: Transport information**

- 14.1. UN number**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packaging group**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**  
not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content &lt; 5 %

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**National regulations/information (Great Britain):**

## Remarks

The Health & Safety at Work Act 1974.  
The Control of Substances Hazardous to Health Regulations. L5:General Approved Code of Practice to the COSHH Regulations. HS(G)97:A Step by Step Guide to the COSHH Regulations. HS(G)193: COSHH essentials: Easy steps to control chemicals.  
IND (G)248L: Solder fume and you. IND(G)249L: Controlling health risks from rosin (colophony) based solder fluxes.  
The Control of Lead at Work Regulations. L132: Control of Lead at Work: Approved Code of Practice and Guidance.  
Employees should be under medical surveillance if the risk assessment made under the Control of Lead at Work Regulations indicates they are likely to be exposed to significant concentrations of lead, or if an Employment Medical Advisor or appointed doctor so certifies.  
A woman employed on work which exposes her to lead should notify her employer as soon as possible if she becomes pregnant. The Employment Medical Advisor / Appointed Doctor should be informed of the pregnancy.  
Under the Management of Health and Safety at Work Regulations, employers are required to assess the particular risks to health at work of pregnant workers and workers who have recently given birth or who are breast feeding.

## SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H317 May cause an allergic skin reaction.
- H360FD May damage fertility. May damage the unborn child.
- H372 Causes damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

### Label elements (DPD):

T - Toxic



### Risk phrases:

- R60 May impair fertility.
- R61 May cause harm to the unborn child.
- R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.
- R43 May cause sensitisation by skin contact.
- R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### Safety phrases:

- S23 Do not breathe fumes.
- S53 Avoid exposure - obtain special instructions before use.
- S45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
- S36/37 Wear suitable protective clothing and gloves.

### Additional labeling:

Restricted to professional users.

### Contains:

- Lead,
- Rosin

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**