

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053002200](#)
Status: **Active**
Overview: [Nano-Fit™ Power Connectors](#)
Description: Nano-Fit™ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-22 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-105300-100 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	105300
Application	Power
Crimp Quality Equipment	Yes
Overview	Nano-Fit™ Power Connectors
Product Name	Nano-Fit™
UPC	889056003292

Physical

Durability (mating cycles max)	50
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	0.100/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.60mm
Wire Size AWG	20, 22
Wire Size mm²	0.30-0.50


Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-105300-100
Sales Drawing	SD-105300-100



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[105300](#) Series

Use With

Nano-Fit™ Receptacle Housing [105307](#) ,
[105308](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description

Product #

FineAdjust™ Applicator for Nano- Fit Terminals	0639032400
--	----------------------------

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION