

SAW Components

SAW RF filter

Short range devices

Series/type: B3588

Ordering code: B39921B3588U410

Date: December 17, 2014

Version: 2.5

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



SAW Components B3588
SAW RF filter 915.0 MHz

Data sheet

SMD


Application

- Low-loss RF filter for remote control receivers
- \blacksquare No matching network required for operation at 50 Ω



Features

- Package size 3.0 x 3.0 x 1.1 mm³
- Package code DCC6C
- RoHS compatible
- Approximate weight 0.037 g
- Package for Surface Mount Technology (SMT)
- Ni, gold-plated terminals
- Lead free soldering compatible with J STD20C
- AEC-Q200 qualified component family
- Electrostatic Sensitive Device (ESD)




Pin configuration

■ 2 Input

■ 5 Output

■ 1, 3, 4, 6 To be ground





SAW Components B3588
SAW RF filter 915.0 MHz

Data sheet <u>SMD</u>

Characteristics

Temperature range for specification: $T = 0 \,^{\circ}C \text{ to } +70 \,^{\circ}C$

Terminating source impedance: $Z_S = 50 \Omega$ Terminating load impedance: $Z_L = 50 \Omega$

		min.	typ. @ 25 °C	max.	
Center frequency	f _C	_	915.0	_	MHz
Maximum insertion attenuation 902.00 928.00 MHz	α_{max}	_	2.9	3.3	dB
Amplitude ripple (p-p) 902.00 928.00 MHz	Δα	_	0.9	1.5	dB
VSWR 902.00 928.00 MHz		_	1.8:1	2.3:1	
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	α_{rel}	50 45 35	55 50 43	_ _ _	dB dB dB
947.00 992.00 MHz 992.00 1020.00 MHz 1020.00 1200.00 MHz		15 35 45	22 45 50	_ _ _	dB dB dB



SAW Components B3588
SAW RF filter 915.0 MHz

Data sheet <u>SMD</u>

Characteristics

Temperature range for specification: $T = -40 \,^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$

Terminating source impedance: $Z_S = 50 \Omega$ Terminating load impedance: $Z_L = 50 \Omega$

		min.	typ. @ 25 °C	max.	
Center frequency	f _C	_	915.0		MHz
Maximum insertion attenuation 902.00 928.00 MHz	α_{max}	_	2.9	3.5	dB
Amplitude ripple (p-p) 902.00 928.00 MHz	Δα	_	0.9	1.8	dB
VSWR 902.00 928.00 MHz		_	1.8:1	2.4:1	
Relative attenuation (relative to α_{max})	α_{rel}				
10.00 800.00 MHz		50	55	_	dB
800.00 845.00 MHz		45	50	_	dB
845.00 880.00 MHz		33	43	_	dB
947.00 992.00 MHz		13	22	_	dB
992.00 1020.00 MHz		35	45	_	dB
1020.00 1200.00 MHz		45	50	_	dB



SAW Components	B3588
SAW RF filter	915.0 MHz
Data sheet	SMD

Maximum ratings

Operable temperature range	T	-45/+125	°C	
Storage temperature range	T_{stg}	-45/+125	°C	
DC voltage	V_{DC}	6	V	
Source power	P_S	15	dBm	source impedance 50 Ω
Source power	n	40	dBm	duty cycle 1:10,
902.00 928.00 MHz	P _S	18		-40 °C to +85 °C



SAW Components B3588

SAW RF filter 915.0 MHz

Data sheet

SMD ESD protection of SAW filters

SAW filters are Electro Static Discharge sensitive devices. To reduce the probability of damages caused by ESD, special matching topologies have to be applied.

In general, "ESD matching" has to be ensured at that filter port, where electrostatic discharge is expected.

Electrostatic discharges predominantly appear at the antenna input of RF receivers. Therefore only the input matching of the SAW filter has to be designed to short circuit or to block the ESD pulse.

Below two figures show recommended "ESD matching" topologies.

Depending on the input impedance of the SAW filter and the source impedance, the needed component values have to be determined from case to case.




Fig. 1 MLC varistor plus ESD matching




Fig. 2 Suppressor diode plus ESD matching

In cases where minor ESD occur, following simplified "ESD matching" topologies can be used alternatively.




Fig. 3 shunt L - series L matching




Fig. 4 series C - shunt L matching

Effectiveness of the applied ESD protection has to be checked according to relevant industry standards or customer specific requirements.

For further information, please refer to EPCOS Application report:

"ESD protection for SAW filters". This report can be found under www.epcos.com/rke. Click on "data sheets" and then "Applications" under category "Further information".




SAW Components

SAW RF filter


915.0 MHz

Data sheet


Transfer function (narrowband)




Transfer function (wideband)







S₂₂ function





SAW Components		B3588
SAW RF filter		915.0 MHz
Data sheet	SMD	

References

Туре	B3588			
Ordering code	B39921B3588U410			
Marking and package	C61157-A7-A67			
Packaging	F61074-V8168-Z000			
Date codes	L_1126			
S-parameters	B3588_NB.s2p, B3588_WB.s2p See file header for port/pin assignment table.			
Soldering profile	S_6001			
RoHS compatible	RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8 th , 2011, on the restriction of the use of certain hazardous substances in electrical and electronic equipment ("Directive") with due regard to the application of exemptions as per Annex III of the Directive in certain cases.			
Matching coils	See Inductor pdf-catalog http://www.tdk.co.jp/tefe02/coil.htm#aname1 and Data Library for circuit simulation http://www.tdk.co.jp/etvcl/index.htm for a large variety of matching coils.			

For further information please contact your local EPCOS sales office or visit our webpage at $\underline{www.epcos.com}$.

Published by EPCOS AG Systems, Acoustics, Waves Business Group P.O. Box 80 17 09, 81617 Munich, GERMANY

© EPCOS AG 2014. This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.



The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.

from the foregoing for customer-specific products.

- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating
- Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.