

151-01857

HellermannTyton

Article Number: 151-01857

Description: Wide Strap Adhesive Mount, .50" Max Tie Width, 1.49" Long/Width, PA66HIRHSUV, Black, 100/pkg



Base Data	Local Order Number	151-01857
	Type	WSMB5AHB
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • For use with 120 pound wide-strap cable ties to provide stability when securing bundles. • Wide slot extends the versatility of our Wide Strap Cable Ties. • Extremely durable adhesive achieves high pull-off force and is unaffected by vibration. • Mount made of proprietary, impact-modified PA66 material for extraordinary durability, and is heat stabilized and UV resistant for extended life outdoors. • Peel and stick for quick, convenient use in extreme-duty applications.
	Quantity Per	bag
	Product Description	HellermannTyton's Wide Strap Adhesive Mount pairs with our exclusive line of Wide Strap Cable Ties and is ideal for extreme-duty applications. The mount features 3M™ VHB™ (Very High Bond) adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.
	Short Description	Wide Strap Adhesive Mount, .50" Max Tie Width, 1.49" Long/Width, PA66HIRHSUV, Black, 100/pkg
Product Dimensions	Length L (Imperial)	1.49"
	Length L (Metric)	37.8mm
	Fixation Method	Adhesive
	Width W (Imperial)	1.49"
	Width W (Metric)	37.7mm
	Cable Tie Width Max. (Imperial)	0.5"
	Cable Tie Width Max. (Metric)	12.7mm
	Height H (Imperial)	0.30"
	Height H (Metric)	7.7mm

151-01857

Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Adhesive	Acrylic foam
	Flammability	UL 94 V2 (excluding adhesive)
	Operating Temperature	-40°F to +176°F (-40°C to +80°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces